

MIRO 6.2 115-1U OUTPUT RELAY WITH LEAKAGE**CURRENT SUPPRESSION**

Art.No.: 52032

Weight: 0.035 kg

Country of origin: CZ

Model designation: MIRO 6,2-1OUTPUT-REL.115V-1U LCS



1 NO/NC contact

6 A

115 V AC/DC

Screw terminals

This module includes a leakage current suppression (LCS) in order to ensure safe shutdown of the module when activated with semiconductors (e.g. Triacs).

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

MIRO 6,2-1OUTPUT-REL.115V-1U LCS

Commercial data	
URL Webshop	https://shop.murrelektronik.com/52032
GTIN	4048879879774
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879879774
Packaging unit	1
Electrical data Input	
Input voltage AC	115 V
Input voltage AC min.	92 V
Input voltage AC max.	132 V
Input voltage DC	115 V
Input voltage DC min.	92 V
Input voltage DC max.	132 V
Input current	8 mA
Electrical data Output	
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	6 A
Switching current DC	100 mA
Power rating AC max.	1.500 VA
Power rating DC max.	120 W
Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24 V 6 A @ 110 V 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V 3 A @ 110 V 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V 0.2 A @ 110 V 0.1 A @ 230 V
Diagnostics	
Status indication LED	green
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Electrical lifetime	0 cycles
Device protection Mechanical	
Mechanical endurance	0 cycles
Mechanical data	
Response time max.	12 ms

Drop-out time max.	5 ms
--------------------	------

Bounce time max.	3 ms
------------------	------

Mechanical data | Material data

Material contact	Ag Sn O ₂
------------------	----------------------

Mechanical data | Mounting data

Height	91 mm
--------	-------

Width	6,2 mm
-------	--------

Depth	71 mm
-------	-------

Mounting method	geschnappt
-----------------	------------

Suitable for mounting type	(EN 60715), mounting rail
----------------------------	---------------------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Connection type 5

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

Connection	Screw terminals SK
------------	--------------------

PIN 1	12
-------	----

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

Connection	Screw terminals SK
------------	--------------------

PIN 1	11
-------	----

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

Connection	Screw terminals SK
------------	--------------------

PIN 1	14
-------	----

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

Connection	Screw terminals SK
------------	--------------------

PIN 1	A 1
-------	-----

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

Connection	Screw terminals SK
------------	--------------------

PIN 1	A 2
-------	-----