

MIRO TH 24VDC SK OPTO-COUPLER MODULE

IN: 50 VDC - OUT: 250 VAC / 0,5A

Art.No.: 52550

Weight: 0.024 kg




Country of origin: CZ


Model designation: MIRO,TH,24VDC,SK

Triac 0.5 A

24 V DC

Screw terminals

[Link to Product](#)**Illustration**



Product may differ from Image



Header	
Material short text	MIRO,TH,24VDC,SK
Commercial data	
URL Webshop	https://shop.murrelektronik.com/52550
GTIN	4048879026789
ECLASS-6.0	27371604
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-7.1	27371604
ECLASS-8.0	27371604
ECLASS-8.1	27371604
ECLASS-9.0	27371604
ECLASS-9.1	27371604
ECLASS-10.0.1	27371604
ECLASS-10.1	27371604
ECLASS-11.0	27371604
ECLASS-11.1	27371604
ECLASS-12.0	27371604
ECLASS-13.0	27371604
ECLASS-14.0	27371604
ETIM-5.0	EC001504
ETIM-6.0	EC001504
ETIM-7.0	EC001504
ETIM-8.0	EC001504
customs tariff number	85414900
EAN	4048879026789
Packaging unit	1
Electrical data Input	
Input voltage DC min.	10 V
Input voltage DC max.	53 V
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	5 V
Current input DC	7 mA

Electrical data Output	
Voltage drop AC max.	1,5 V
Quiescent current OFF max.	0,3 mA
Switch on delay max.	10 ms
Switch off delay max.	10 ms
Voltage switching AC min.	24 V
Switching voltage AC max.	250 V
Switching current min.	1,5 mA
Switching current max.	0,5 A
Switching frequency max.	20 Hz
Additional condition switching frequency	depending on wiring
Diagnostics	
Status indication LED	yellow
Device protection Electrical	
Rated surge voltage	2,5 kV
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Material housing	Plastic
Color housing	black
Mechanical data Mounting data	
Height	78 mm
Width	6,2 mm
Depth	70 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Connection type 4	
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Screw terminals SK
PIN 1	13
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Screw terminals SK
PIN 1	14
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Screw terminals SK
PIN 1	A 1
Family construction form	terminal
No. of poles	1
Gender	female

Color contact carrier	black
Connection	Screw terminals SK
PIN 1	A 2