

IMPACT67 Pro PN DIO8 IOL8 M12L 4P




PROFINET, compact module, plastic

Art.No.: 54620
 Weight: 0.470 kg
 Country of origin: DE
 Model designation: IMPACT67 Pro PN DIO8 IOL8 M12L 4P

Digital inputs/outputs
 Ethernet 10/100 Mbit/s; M12, D-coded
 IO-Link Master V1.1
 M12 Power, 4-pole, L-coded
 M12, 5-pole, A-coded
 Housing fully potted.
 Connection cables are in the online shop under "Connection Technology".
 mounting compatible with I/O modules of the MVK series

[Link to Product](#)

Illustration



Product may differ from Image



Header

The information in this Product-PDF has been compiled with the utmost care.
 Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-02-11

Material short text	IMPACT67 Pro PN DIO8 IOL8 M12L 4P
Commercial data	
URL Webshop	https://shop.murrelektronik.com/54620
GTIN	4065909022832
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-7.1	27242604
ECLASS-8.0	27242604
ECLASS-8.1	27242604
ECLASS-9.0	27242604
ECLASS-9.1	27242604
ECLASS-10.0.1	27242604
ECLASS-10.1	27242604
ECLASS-11.0	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ECLASS-13.0	27242604
ECLASS-14.0	27242604
ETIM-5.0	EC001597
ETIM-6.0	EC001597
ETIM-7.0	EC001597
ETIM-8.0	EC001597
customs tariff number	85389099
EAN	4065909022832
Packaging unit	1
Electrical data Supply	
Norm operating voltage	IEC/EN 61131-2
Operating voltage US DC	24 V
Total current US max.	16 A
Operating voltage UA DC	24 V
Total current UA max.	16 A
Electrical data Input	
Sensor current US per input max.	2 A
Current carrying capacity max.	10 A
Short-circuit protected	Yes
Overload resistant	Yes
Type input	for 3-wire sensors or mechanical switches, IO-Link Devices, PNP
Electrical data Output	
Output current per pin max.	2 A
Max. current output per port	4 A
Actuator current UA per output max.	2 A
Total current outputs max.	10 A
Overload resistant	Yes
Short-circuit protected	Yes
Industrial Communication	
Supported protocol	Profinet
Web interface	Yes
Industrial communication Profinet	
PROFINET conformance class	C
PROFINET addressing	DCP

PROFINET Netload Class	III
PROFINET specification	V2.3
IRT (network communication)	Yes
Shared device/input	Yes
Number of active connections (IO controller) max.	2

Industrial communication | IO-Link

IO-Link type	8× Master
Port Class	A, B
IO-Link transmission rate	COM1, COM2, COM3
IO-Link process data length input	32 bytes
IO-Link process data length output	32 bytes
Automatic baudrate detection	Yes

Industrial communication | IIoT functions

JSON integration	REST-API, MQTT
OPC UA transport	UA TCP, UA Binary Encoding, UA Secure Conversation
Publishing interval OPC UA min.	100 ms
Number of sessions / clients OPC UA max.	5
Voltage monitoring	Yes
Current Monitoring	Yes

Diagnostics

Actuator warning	per channel via LED and BUS
Temperature control	Yes
Cable break	per port
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module and channel
LED display	Ethernet connection/data traffic
IO-Link events	Undervoltage supply, No voltage

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data | Mounting data

Height	37 mm
Width	63 mm
Depth	225 mm
Suitable for mounting type	2-hole screw mounting

Environmental characteristics | Climatic

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage, transport)	-40 °C ... 85 °C

Connection type 4

Connection type 1	X0-X7
Connection type 2	XD1
Connection type 3	XD2
Connection type 4	XF1, XF2
Family construction form	M12
No. of poles	5
Coding	A
Gender	female
Color contact carrier	gray
PIN 1	24 V DC
PIN 2	DI / DO
PIN 3	0 V

PIN 4	DI / DO / IO-Link
PIN 5	0 V
Family construction form	M12
No. of poles	5
Coding	L
Gender	male
Color contact carrier	black
PIN 1	24 V DC (US)
PIN 2	0 V
PIN 3	0 V
PIN 4	24 V DC (UA)
PIN 5	n.c.
Family construction form	M12
No. of poles	4
Coding	L
Gender	female
Color contact carrier	black
PIN 1	24 V DC (US)
PIN 2	0 V
PIN 3	0 V
PIN 4	24 V DC (UA)
Family construction form	M12
No. of poles	4
Coding	D
Gender	female
Color contact carrier	black
Mounting method	inserted, screwed
Tightening torque	0,6 Nm
PIN 1	TD +
PIN 2	RD +
PIN 3	TD -
PIN 4	RD -
PIN 5	n.c.