

CAN-PLUG-MALE (SUB-D) 90°

Screw terminals up to 1Mbit/s

Art.No.: 55760

Weight: 0.046 kg

Country of origin: DE

Model designation: CAN Stecker 90° Schraubklemmen

Bus connection plug 90°

SUB-D9 (female), screw terminals

max. 1 Mbit/s with switchable terminal resistors

CANopen

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



Product may differ from Image

Header

Material short text CAN Stecker 90° Schraubklemmen

Commercial data

URL Webshop	https://shop.murrelektronik.com/55760
GTIN	4048879049825
ECLASS-6.0	27279221
ECLASS-6.1	27242692
ECLASS-7.0	27242692
ECLASS-7.1	27242692
ECLASS-8.0	27242692
ECLASS-8.1	27242692
ECLASS-9.0	27242692
ECLASS-9.1	27242692
ECLASS-10.0.1	27242692
ECLASS-10.1	27242692
ECLASS-11.0	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ECLASS-13.0	27242692
ECLASS-14.0	27242692
ETIM-5.0	EC002584

ETIM-6.0	EC002584
ETIM-7.0	EC002584
ETIM-8.0	EC002584
customs tariff number	85366990
EAN	4048879049825
Packaging unit	1
Electrical data	
Terminating resistor	integrated, connectable
Industrial Communication	
Data transmission rate max.	1 Mbit/s
Installation	
Connection cross section max.	1 mm ²
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Height	65 mm
Width	48 mm
Depth	16 mm
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-25 °C
Important installation notes	
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Connection type 2	
Family construction form	D-Sub
No. of poles	9
Gender	female
PIN 2	CAN_L
PIN 3	CAN_GND
PIN 5	CAN_SHLD
PIN 6	0 V
PIN 7	CAN_H
PIN 9	CAN V +
Family construction form	terminal
No. of poles	6
Gender	female
Connection	Screw terminals SK