

EOL - Cube67 Valve-Interface, I/O Extension Module

discontinued - End of Life Date: 2024-12-31

Art.No.: 5665112

Weight: 0.260 kg

Country of origin: CZ

Model designation: X Cube67 DO16 E Valve V 20/22 B

Expansion module

DO16 - Valve (E) 0.5 m

Multipole plug (70 mA)

NORGREN - V20/22B

Connection cables are in the online shop under "Connection Technology".


Housing fully potted.

Link to Product

Illustration



Product may differ from Image



Header

Material short text X Cube67 DO16 E Valve V 20/22 B

Commercial data

URL Webshop	https://shop.murrelektronik.com/5665112
GTIN	4048879045186
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-7.1	27242604
ECLASS-8.0	27242604
ECLASS-8.1	27242604
ECLASS-9.0	27242604
ECLASS-9.1	27242604
ECLASS-10.0.1	27242604
ECLASS-10.1	27242604
ECLASS-11.0	27242604
ECLASS-11.1	27242604

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-02-09

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

ECLASS-12.0	27242604
ECLASS-13.0	27242604
ECLASS-14.0	27242604
customs tariff number	85389099
EAN	4048879045186
Packaging unit	1

Electrical data | Supply

Norm operating voltage	IEC/EN 61131-2
Total current US max.	4 A
Operating voltage UA DC	24 V
Total current UA max.	4 A
Current consumption max.	50 mA

Electrical data | Output

Output current per pin max.	0,05 A
Overload resistant	Yes
Short-circuit protected	Yes

Diagnostics

Actuator warning	per channel via BUS
Short circuit diagnosis	Yes
Overload diagnosis	Yes
Diagnostic	No voltage, Under voltage
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module
LED display	Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data | Mounting data

Height	150 mm
Width	30 mm
Depth	34,5 mm
Suitable for mounting type	2-hole screw mounting

Environmental characteristics | Climatic

Operating temperature max.	55 °C
Ambient temperature (storage, transport)	-20 °C

Connection type 1

Connection type 1	Bus In
Connection type 2	Bus Out
Connection type 3	Data
Family construction form	D-Sub
No. of poles	25
Gender	male
PIN 1	Out 1
PIN 3	Out 2
PIN 5	Out 3
PIN 7	Out 4
PIN 9	Out 5
PIN 10	Out 6
PIN 11	Out 7
PIN 12	Out 8
PIN 13	Out 9
PIN 14	Out 10

PIN 15	Out 11
PIN 16	Out 12
PIN 17	Out 13
PIN 18	Out 14
PIN 19	Out 15
PIN 20	Out 16
PIN 24	0 V
PIN 25	Sens