

TERMINAL MODULE CUBE67 IP20

8 digital inputs, 8 multifunction channels

Art.No.: 56691

Weight: 0.150 kg

Country of origin: CZ

Model designation: Cube67 DIO8/DI8 E TB Rail

Terminal module

DIO8/DI8 - (E) TB-Rail

Connection cables are in the online shop under "Connection Technology".


Housing fully potted.

[Link to Product](#)

Illustration



Product may differ from Image



Header

Material short text Cube67 DIO8/DI8 E TB Rail

Commercial data

URL Webshop <https://shop.murrelektronik.com/56691>

GTIN 4048879048279

ECLASS-6.0 27242604

ECLASS-6.1 27242604

ECLASS-7.0 27242604

ECLASS-7.1 27242604

ECLASS-8.0 27242604

ECLASS-8.1 27242604

ECLASS-9.0 27242604

ECLASS-9.1 27242604

ECLASS-10.0.1 27242604

ECLASS-10.1 27242604

ECLASS-11.0 27242604

ECLASS-11.1 27242604

ECLASS-12.0 27242604

ECLASS-13.0	27242604
ECLASS-14.0	27242604
ETIM-5.0	EC001599
ETIM-6.0	EC001599
ETIM-7.0	EC001599
ETIM-8.0	EC001599
customs tariff number	85389099
EAN	4048879048279
Packaging unit	1

Electrical data | Supply

Norm operating voltage	IEC/EN 61131-2
Operating voltage US DC	24 V
Total current US max.	4 A
Operating voltage UA DC	24 V
Total current UA max.	4 A
Current consumption max.	50 mA

Electrical data | Input

Sensor current US per input max.	0,2 A
Input filter time	1 ms
Type input	for 3-wire sensors or mechanical switches, PNP

Electrical data | Output

Output current per pin max.	0,5 A
Overload resistant	Yes
Short-circuit protected	Yes
Lamp load	10 W

Diagnostics

Actuator warning	per channel via LED and BUS
Short circuit diagnosis	Yes
Overload diagnosis	Yes
Diagnostic	No voltage, Under voltage
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module and channel
LED display	Ethernet connection/data traffic

Installation | Pin assignment

Terminal row X0	Input
Terminal row X1	Input/Output

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Height	113 mm
Width	54 mm
Depth	45 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Ambient temperature (storage, transport)	-20 °C ... 75 °C

Connection type 6

Connection type 1	Bus In
Connection type 2	Bus Out

Connection type 3	X0
Connection type 4	X1
Connection type 5	X2
Connection type 6	X3
Family construction form	M12
No. of poles	6
Coding	A
Gender	male
Color contact carrier	black
PIN 1	24 V DC (UA)
PIN 2	24 V DC (US)
PIN 3	0 V
PIN 4	Bus internal
PIN 5	Bus internal
PIN 6	0 V
Family construction form	M12
No. of poles	6
Coding	A
Gender	female
Color contact carrier	black
PIN 1	24 V DC (UA)
PIN 2	24 V DC (US)
PIN 3	0 V
PIN 4	Bus internal
PIN 5	Bus internal
PIN 6	0 V
Family construction form	terminal
No. of poles	8
Gender	female
Color contact carrier	colorless
Connection	Spring clamp terminals FK
PIN 1	DI 10
PIN 2	DI 11
PIN 3	DI 12
PIN 4	DI 13
PIN 5	DI 14
PIN 6	DI 15
PIN 7	DI 16
PIN 8	DI 17
Family construction form	terminal
No. of poles	8
Gender	female
Color contact carrier	colorless
Connection	Spring clamp terminals FK
PIN 1	DI / DO 00
PIN 2	DI / DO 01
PIN 3	DI / DO 02
PIN 4	DI / DO 03
PIN 5	DI / DO 04
PIN 6	DI / DO 05
PIN 7	DI / DO 06
PIN 8	DI / DO 07
Family construction form	terminal
No. of poles	8

Gender	female
Color contact carrier	colorless
Connection	Spring clamp terminals FK
PIN 1	24 V DC (US) 00
PIN 2	24 V DC (US) 01
PIN 3	24 V DC (US) 02
PIN 4	24 V DC (US) 03
PIN 5	24 V DC (US) 04
PIN 6	24 V DC (US) 05
PIN 7	24 V DC (US) 06
PIN 8	24 V DC (US) 07
Family construction form	terminal
No. of poles	8
Gender	female
Color contact carrier	colorless
Connection	Spring clamp terminals FK
PIN 1	0 V 00
PIN 2	0 V 01
PIN 3	0 V 02
PIN 4	0 V 03
PIN 5	0 V 04
PIN 6	0 V 05
PIN 7	0 V 06
PIN 8	0 V 07