

CUBE20S POWER MODULE

24VDC + 5VDC/2A

Art.No.: 57131

Weight: 0.085 kg

Country of origin: DE

Model designation: Cube20S Power module 24VDC+5VDC/2A


Power module

Expansion module

for external voltage supply and internal backplane

Link to Product**Illustration**

Product may differ from Image

**Commercial data**

URL Webshop	https://shop.murrelektronik.com/57131
GTIN	4048879422895
Customs tariff number	85369010
ECLASS-6.0	27242610
ECLASS-6.1	27242611
ECLASS-7.0	27242611
ECLASS-7.1	27242611
ECLASS-8.0	27242611
ECLASS-8.1	27242611
ECLASS-9.0	27242611
ECLASS-9.1	27242611
ECLASS-10.0.1	27242611
ECLASS-10.1	27242611
ECLASS-11.0	27242611
ECLASS-11.1	27242611
ECLASS-12.0	27242611
ECLASS-13.0	27242611
ECLASS-14.0	27242611
ETIM-5.0	EC001600

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-04-18

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

ETIM-6.0	EC001600
ETIM-7.0	EC001600
ETIM-8.0	EC001600
customs tariff number	85369010
EAN	4048879422895
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Total current max.	6 A
Electrical data Input	
Input voltage DC	24 V
Input voltage DC min.	20,4 V
Input voltage DC max.	28,8 V
Electrical data Output	
Output voltage DC	24 V
Output current	4 A
Current output backplane bus max.	2 A
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Height	109 mm
Width	12,9 mm
Depth	76,5 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-25 °C ... 70 °C
Connection type 1	
Connection type 1	Power
Family construction form	terminal
No. of poles	8
Gender	female
Connection	Spring clamp terminals FK
PIN 1	n.c.
PIN 2	24 V DC
PIN 3	0 V
PIN 4	24 V DC Sys
PIN 5	n.c.
PIN 6	24 V DC
PIN 7	0 V
PIN 8	0 V Sys