

6 Port unmanaged Gigabit Switch 4 PoE 1 SFP Ports IP20 metal 48V

Art.No.: 58191

Weight: 0.350 kg



Country of origin: TW

Model designation: TREE 6TX 4PoE 1SFP GE 48V

6 Port Unmanaged IP20 PoE Gigabit Switch

48 V power supply

SFP contact holder

Link to Product**Illustration**

Product may differ from Image

**Header**

Material short text

TREE 6TX 4PoE 1SFP GE 48V

Commercial data

URL Webshop

<https://shop.murrelektronik.com/58191>

GTIN

4048879843683

ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-7.1	19170106
ECLASS-8.0	19170106
ECLASS-8.1	19170106
ECLASS-9.0	19170402
ECLASS-9.1	19170106
ECLASS-10.0.1	19170402
ECLASS-10.1	19170402
ECLASS-11.0	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
ECLASS-13.0	19170402
ECLASS-14.0	19170402
customs tariff number	85176200
EAN	4048879843683
Packaging unit	1
Electrical data Supply	
Power consumption max.	7,2 W
PoE voltage amplifier	Yes
Industrial Communication	
Data transmission rate max.	1.000 Mbit/s
Industrial communication Ethernet functionality	
VLAN unmanaged (IEEE 802.1Q)	Yes
Switch type	unmanaged
duplex	Full duplex
Auto-negotiation	Yes
Auto-crossover	Yes
Diagnostics	
Alarm contact	Yes
Diagnostic	No voltage
LED display	Ethernet connection/data traffic
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Material data	
Material housing	Metal
Color housing	black
Mechanical data Mounting data	
Height	110 mm
Width	45,4 mm
Depth	89,6 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	70 °C
Ambient temperature (storage, transport)	-40 °C
Connection type 3	
Connection type 1	1
Connection type 2	6

Connection type 3	X1
Family construction form	POF SC-RJ
No. of poles	2
Gender	female
Color contact carrier	black
PIN 1	RD
PIN 2	TD
Family construction form	RJ45
No. of poles	8
Gender	female
Color contact carrier	black
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.
Family construction form	terminal
No. of poles	7
Gender	male
Color contact carrier	green
Connection	Plug-in terminals RK
PIN 1	V 2 +
PIN 2	V 2 -
PIN 3	Relay (NO)
PIN 4	Relay (NO)
PIN 5	V 1 +
PIN 6	V 1 -
PIN 7	FE