


Xelity 6TX GE Unmanaged Switch 6 Port 1000Mbit

Art.No.: 58814
Weight: 0.151 kg
Country of origin: DE
Model designation: Xelity 6TX GE

6 port unmanaged switch
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	Xelity 6TX GE
Commercial data	
URL Webshop	https://shop.murrelektronik.com/58814
GTIN	4065909013236
ECLASS-7.1	19170106
ECLASS-8.1	19170106

ECLASS-9.1	19170106
ECLASS-10.0.1	19170401
ECLASS-11.0	19170401
ECLASS-13.0	19170401
ECLASS-14.0	19170401
customs tariff number	85176200
EAN	4065909013236
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	9 V
Operating voltage DC max.	30 V

Industrial Communication

Data transmission rate max.	1.000 Mbit/s
-----------------------------	--------------

Industrial communication | Ethernet functionality

VLAN unmanaged (IEEE 802.1Q)	Tag forwarding
Switch type	unmanaged
duplex	Full duplex
Auto-negotiation	Yes
Auto-crossover	Yes

Diagnostics

Alarm contact	No
Diagnostic	No voltage
LED display	Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Material data

Material housing	Plastic
Color housing	black

Mechanical data | Mounting data

Height	140 mm
Width	30 mm
Depth	85,1 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	75 °C
Ambient temperature (storage, transport)	-40 °C ... 85 °C

Connection type 2

Connection type 1	6
Family construction form	RJ45
No. of poles	8
Gender	female
Color contact carrier	black
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -

PIN 7	n.c.
PIN 8	n.c.
Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	24 V DC (UB 1)
PIN 2	0 V
PIN 3	PE
PIN 4	n.c.