

Emergency-stop pushbutton with 2 positive opening contacts

in a IP65 enclosure

Art.No.: 69040

Weight: 0.193 kg

Country of origin: DE

Model designation: E-Stop 72P 2NC M12(4)

E-Stop 72P 2NC M12(4)



with M12 connection

4-pole


Emergency-Stop button

2 NC (positively-opening)

with protection shroud

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

E-Stop 72P 2NC M12(4)

Commercial data	
URL Webshop	https://shop.murrelektronik.com/69040
GTIN	4048879594806
ECLASS-6.0	27371244
ECLASS-6.1	27371244
ECLASS-7.0	27371244
ECLASS-7.1	27371244
ECLASS-8.0	27371244
ECLASS-8.1	27371244
ECLASS-9.0	27371244
ECLASS-9.1	27371244
ECLASS-10.0.1	27371244
ECLASS-10.1	27371244
ECLASS-11.0	27371244
ECLASS-11.1	27371244
ECLASS-12.0	27371244
ECLASS-13.0	27371244
ECLASS-14.0	27371244
ETIM-5.0	EC002034
ETIM-6.0	EC002034
ETIM-7.0	EC002034
ETIM-8.0	EC002034
customs tariff number	85365080
EAN	4048879594806
Packaging unit	1
Electrical data Output	
Switching current (AC-15)	30 A
Switching current (DC-13)	2,2 A
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 250 V
Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V
Device protection	
Condition lifetime	load-dependent, temperature dependent
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	0 cycles
Device protection Mechanical	
Mechanical endurance	0 cycles
Operating life B10d	250.000 cycles
Mechanical data	
Bounce time max.	9 ms
Mechanical data Material data	
Material contact	AgNi
Mechanical data Mounting data	
Height	104 mm
Width	72 mm
Depth	91 mm
Mounting method	screwed
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C

Ambient temperature (storage, transport) -25 °C ... 85 °C

Technical Data | Reliability

Lambda normally closed contact 20 %

Connection type 1

Family construction form M12

No. of poles 4

Coding A

Gender male

Color contact carrier black

PIN 1 NC 1

PIN 2 NC 1

PIN 3 NC 2

PIN 4 NC 2