

Illuminated Emergency-stop pushbutton with 2 positive opening contacts

in a IP65 enclosure

Art.No.: 69043

Weight: 0.195 kg

Country of origin: DE

Model designation: E-Stop 72 2NC L M12(8)

E-Stop 72 2NC L M12(8)

with M12 connection

8-pole




Emergency-Stop button

2 NC (positively-opening)

LED-Ring can be lit

[Link to Product](#)

Illustration



Product may differ from Image



Header

Material short text

E-Stop 72 2NC L M12(8)

Commercial data	
URL Webshop	https://shop.murrelektronik.com/69043
GTIN	4048879594813
ECLASS-6.0	27371244
ECLASS-6.1	27371244
ECLASS-7.0	27371244
ECLASS-7.1	27371244
ECLASS-8.0	27371244
ECLASS-8.1	27371244
ECLASS-9.0	27371244
ECLASS-9.1	27371244
ECLASS-10.0.1	27371244
ECLASS-10.1	27371244
ECLASS-11.0	27371244
ECLASS-11.1	27371244
ECLASS-12.0	27371244
ECLASS-13.0	27371244
ECLASS-14.0	27371244
ETIM-5.0	EC002034
ETIM-6.0	EC002034
ETIM-7.0	EC002034
ETIM-8.0	EC002034
customs tariff number	85365080
EAN	4048879594813
Packaging unit	1
Electrical data	
Operating voltage AC/DC LED illumination min.	12 V
Operating voltage AC/DC LED illumination max.	30 V
Operating current LED illumination	15 mA @ 24 V AC/DC
Electrical data Output	
Switching current (AC-15)	30 A
Switching current (DC-13)	2,2 A
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 250 V
Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V
Device protection	
Condition lifetime	load-dependent, temperature dependent
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	0 cycles
Device protection Mechanical	
Mechanical endurance	0 cycles
Operating life B10d	250.000 cycles
Mechanical data	
Bounce time max.	9 ms
Mechanical data Material data	
Material contact	AgNi
Mechanical data Mounting data	
Height	103 mm
Width	72 mm
Depth	91 mm

Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-25 °C ... 85 °C
Technical Data Reliability	
Lambda normally closed contact	20 %
Connection type 1	
Family construction form	M12
No. of poles	8
Coding	A
Gender	male
Color contact carrier	black
PIN 1	NC 1
PIN 2	NC 1
PIN 3	NC 2
PIN 4	NC 2
PIN 7	X 2 -
PIN 8	X 1 +