

MSUD valve plug BI-11mm with cable

PVC 3x0.75 bk 0.3m

Art.No.: 7000-11021-6160030

Weight: 0.050 kg

Country of origin: CZ

Model designation: MSUDS-IB1Z-616_0.3

MSUD

Form BI (11 mm)




 24 V AC $\pm 20\%$ / DC $\pm 25\%$


LED and suppression

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)
Illustration




Product may differ from Image



Header

Material short text	MSUDS-IB1Z-616_0.3
---------------------	--------------------

Cable length	0,30 m
--------------	--------

Side 1

Family construction form	Valve connector form B1
--------------------------	-------------------------

No. of poles	3
--------------	---

Gender	female
--------	--------

Mounting method	inserted, screwed
-----------------	-------------------

Threaded hole	M3x31
---------------	-------

Tightening torque	0,4 Nm
-------------------	--------

Material	PBT
----------	-----

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-11021-6160030
-------------	---

GTIN	4048879221573
------	---------------

ECLASS-6.0	27279218
------------	----------

ECLASS-6.1	27279218
------------	----------

ECLASS-7.0	27279218
------------	----------

ECLASS-7.1	27279218
------------	----------

ECLASS-8.0	27279218
------------	----------

ECLASS-8.1	27279218
------------	----------

ECLASS-9.0	27060312
------------	----------

ECLASS-9.1	27060312
------------	----------

ECLASS-10.0.1	27060312
---------------	----------

ECLASS-10.1	27060312
-------------	----------

ECLASS-11.0	27060312
-------------	----------

ECLASS-11.1	27060312
-------------	----------

ECLASS-12.0	27060312
-------------	----------

ECLASS-13.0	27060312
-------------	----------

ECLASS-14.0	27060312
-------------	----------

ETIM-5.0	EC001855
----------	----------

ETIM-6.0	EC001855
----------	----------

ETIM-7.0	EC001855
----------	----------

ETIM-8.0	EC001855
customs tariff number	85444290
EAN	4048879221573
Packaging unit	1

Electrical data

Drop-out delay time max.	20 ms
--------------------------	-------

Electrical data | Supply

Operating voltage AC	24 V
Operating voltage AC min.	19,2 V
Operating voltage AC max.	28,8 V
Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Current operating per contact max.	4 A
Cut-off peak voltage max.	55 V
Current consumption max.	15 mA

Diagnostics

Status indication LED	yellow
-----------------------	--------

Installation | Connection

Mounting set	M3x31
--------------	-------

Device protection | Electrical

Additional condition protection degree	inserted, screwed
Pollution Degree	3
Additional suppressor	Diode, Z-Diode
Rated surge voltage	0,8 kV
Material group (IEC 60664-1)	I

Mechanical data | Material data

Color housing	black
Material screw connection	Steel
Coating of fitting	galvanized
Locking material	Steel
Coating locking	galvanized
Material gasket	PUR

Mechanical data | Mounting data

Mounting method	inserted, screwed
-----------------	-------------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
------------------------	---

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
-----------------------	---

Installation | Cable

Cable identification	616
Cable Type	1
Stranding	1 x 3 wires stranded
Cable weight	56 g/m
Material wire insulation	PVC
Amount wires	3

Outer diameter insulation	1,8 mm
Outer diameter tolerance core insulation	± 0,1 mm
Shore hardness wire insulation	43 ± 5 Shore D
Material properties wire insulation	good machinability
Ingredient freeness wire insulation	lead-free, cadmium-free, CFC-free, silicone-free
Printing color of wire insulation	white (isolation black)
Amount strands (wire)	24
Diameter of single wires	0,2 mm
Conductor crosssection (wire)	0,75 mm ²
Material conductor wire	Stranded copper wire, bare
Conductor type (wire)	Strand class 5
Outer-diameter (jacket)	5,9 mm
Tolerance outer diameter (sheath)	± 5 %
Material jacket	PVC
Shore hardness jacket	80 ± 5 Shore A
Freedom from ingredients (jacket)	lead-free, cadmium-free, CFC-free, silicone-free
Material property (jacket)	good machinability
Conductor resistance (wire)	26 Ω/km @ 20 °C
Max. rated voltage (conductor - ground)	300 V
Max. rated voltage (conductor - conductor)	500 V
Withstand voltage (wire - wire)	3 kV @ 60 s
Withstand voltage (wire - jacket)	3 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity max. (wire)	12 A
Operating temperature min. (static)	-30 °C
Operating temperature max. (static)	70 °C
Operating temperature min. (dynamic)	-5 °C
Operating temperature max. (dynamic)	70 °C
Oil resistance	good
Chemical resistance	good
Other resistances	good resistance to gasoline
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter