



Non-reversing motor starter Size 3 1/2 Three phase full voltage Solid-state overload relay OLRelay amp range 50-200A 220-240/440-480VAC 60HZ coil Combination type No enclosure

|                                                                         |                                                             |
|-------------------------------------------------------------------------|-------------------------------------------------------------|
| product brand name                                                      | Class 14                                                    |
| design of the product                                                   | Full-voltage non-reversing motor starter                    |
| special product feature                                                 | ESP200 overload relay; Half-size starter; Dual voltage coil |
| <b>General technical data</b>                                           |                                                             |
| weight [lb]                                                             | 8 lb                                                        |
| Height x Width x Depth [in]                                             | 9.78 × 6.75 × 5.19 in                                       |
| touch protection against electrical shock                               | Not finger-safe                                             |
| installation altitude [ft] at height above sea level maximum            | 6560 ft                                                     |
| ambient temperature [°F]                                                |                                                             |
| • during storage                                                        | -22 ... +149 °F                                             |
| • during operation                                                      | -4 ... +104 °F                                              |
| ambient temperature                                                     |                                                             |
| • during storage                                                        | -30 ... +65 °C                                              |
| • during operation                                                      | -20 ... +40 °C                                              |
| country of origin                                                       | Mexiko                                                      |
| <b>Horsepower ratings</b>                                               |                                                             |
| yielded mechanical performance [hp] for 3-phase AC motor                |                                                             |
| • at 200/208 V rated value                                              | 30 hp                                                       |
| • at 220/230 V rated value                                              | 40 hp                                                       |
| • at 460/480 V rated value                                              | 75 hp                                                       |
| • at 575/600 V rated value                                              | 75 hp                                                       |
| <b>Contactors</b>                                                       |                                                             |
| size of contactor                                                       | Controller half size 3 1/2                                  |
| number of NO contacts for main contacts                                 | 3                                                           |
| operating voltage for main current circuit at AC at 60 Hz maximum       | 600 V                                                       |
| operational current at AC at 600 V rated value                          | 115 A                                                       |
| mechanical service life (operating cycles) of the main contacts typical | 5000000                                                     |
| <b>Auxiliary contact</b>                                                |                                                             |
| number of NC contacts at contactor for auxiliary contacts               | 0                                                           |
| number of NO contacts at contactor for auxiliary contacts               | 1                                                           |
| number of total auxiliary contacts maximum                              | 7                                                           |
| contact rating of auxiliary contacts of contactor according to UL       | 10A@600VAC (A600), 2.5A@300VDC (Q300)                       |
| <b>Coil</b>                                                             |                                                             |
| type of voltage of the control supply voltage                           | AC                                                          |
| control supply voltage                                                  |                                                             |
| • at AC at 60 Hz rated value                                            | 220 ... 480 V                                               |
| holding power at AC minimum                                             | 14 W                                                        |

|                                                                                                                    |                                      |
|--------------------------------------------------------------------------------------------------------------------|--------------------------------------|
| apparent pick-up power of magnet coil at AC                                                                        | 310 VA                               |
| apparent holding power of magnet coil at AC                                                                        | 26 VA                                |
| operating range factor control supply voltage rated value of magnet coil                                           | 0.85 ... 1.1                         |
| percentual drop-out voltage of magnet coil related to the input voltage                                            | 50 %                                 |
| ON-delay time                                                                                                      | 26 ... 41 ms                         |
| OFF-delay time                                                                                                     | 14 ... 19 ms                         |
| <b>Overload relay</b>                                                                                              |                                      |
| product function                                                                                                   |                                      |
| • overload protection                                                                                              | Yes                                  |
| • phase failure detection                                                                                          | Yes                                  |
| • asymmetry detection                                                                                              | Yes                                  |
| • ground fault detection                                                                                           | Yes                                  |
| • test function                                                                                                    | Yes                                  |
| • external reset                                                                                                   | No                                   |
| reset function                                                                                                     | Manual, automatic and remote         |
| trip class                                                                                                         | CLASS 5 / 10 / 20 (factory set) / 30 |
| adjustable current response value current of the current-dependent overload release                                | 50 ... 200 A                         |
| tripping time at phase-loss maximum                                                                                | 3 s                                  |
| relative repeat accuracy                                                                                           | 1 %                                  |
| product feature protective coating on printed-circuit board                                                        | Yes                                  |
| number of NC contacts of auxiliary contacts of overload relay                                                      | 1                                    |
| number of NO contacts of auxiliary contacts of overload relay                                                      | 1                                    |
| operational current of auxiliary contacts of overload relay                                                        |                                      |
| • at AC at 600 V                                                                                                   | 5 A                                  |
| • at DC at 250 V                                                                                                   | 1 A                                  |
| contact rating of auxiliary contacts of overload relay according to UL                                             | 5A@600VAC (B600), 1A@250VDC (R300)   |
| insulation voltage (Ui)                                                                                            |                                      |
| • with single-phase operation at AC rated value                                                                    | 600 V                                |
| • with multi-phase operation at AC rated value                                                                     | 300 V                                |
| <b>Enclosure</b>                                                                                                   |                                      |
| degree of protection NEMA rating of the enclosure                                                                  | Open device (no enclosure)           |
| design of the housing                                                                                              | NA                                   |
| <b>Mounting/wiring</b>                                                                                             |                                      |
| mounting position                                                                                                  | vertical                             |
| fastening method                                                                                                   | Surface mounting and installation    |
| type of electrical connection for supply voltage line-side                                                         | lug                                  |
| tightening torque [lbf-in] for supply                                                                              | 120 lbf-in                           |
| type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded                  | 1x(14 - 2/0 AWG)                     |
| temperature of the conductor for supply maximum permissible                                                        | 75 °C                                |
| material of the conductor for supply                                                                               | Al or Cu                             |
| type of electrical connection for load-side outgoing feeder                                                        | Box lug                              |
| tightening torque [lbf-in] for load-side outgoing feeder                                                           | 120 lbf-in                           |
| type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded | 1x(14 - 2/0 AWG)                     |
| temperature of the conductor for load-side outgoing feeder maximum permissible                                     | 75 °C                                |
| material of the conductor for load-side outgoing feeder                                                            | Al or Cu                             |
| type of electrical connection of magnet coil                                                                       | screw terminal                       |
| tightening torque [lbf-in] at magnet coil                                                                          | 5 ... 12 lbf-in                      |
| type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded                | 2 x (16 - 12 AWG)                    |
| temperature of the conductor at magnet coil maximum permissible                                                    | 75 °C                                |
| material of the conductor at magnet coil                                                                           | Cu                                   |
| type of electrical connection for auxiliary contacts                                                               | screw terminal                       |
| tightening torque [lbf-in] at contactor for auxiliary contacts                                                     | 10 ... 15 lbf-in                     |

|                                                                                                                                                            |                                                     |
|------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------|
| type of connectable conductor cross-sections at contactor for AWG cables for auxiliary contacts single or multi-stranded                                   | 1 x (12 AWG), 2 x (16 - 14 AWG), 2 x (18 - 16 AWG)  |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible                                                                       | 75 °C                                               |
| material of the conductor at contactor for auxiliary contacts                                                                                              | Cu                                                  |
| type of electrical connection at overload relay for auxiliary contacts                                                                                     | screw terminal                                      |
| tightening torque [lbf-in] at overload relay for auxiliary contacts                                                                                        | 7 ... 10 lbf-in                                     |
| type of connectable conductor cross-sections at overload relay for AWG cables for auxiliary contacts single or multi-stranded                              | 2 x (20 - 14 AWG)                                   |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible                                                                  | 75 °C                                               |
| material of the conductor at overload relay for auxiliary contacts                                                                                         | Cu                                                  |
| <b>Short-circuit current rating</b>                                                                                                                        |                                                     |
| design of the fuse link for short-circuit protection of the main circuit required                                                                          | 10kA@600V (Class H or K); 100kA@600V (Class R or J) |
| design of the short-circuit trip                                                                                                                           | thermo magnetisch                                   |
| maximum short-circuit current breaking capacity (Icu) <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 480 V</li> <li>• at 600 V</li> </ul> | 14 kA<br>10 kA<br>10 kA                             |
| certificate of suitability                                                                                                                                 | NEMA ICS 2; UL 508; CSA 22.2, No.14                 |
| <b>Approvals Certificates</b>                                                                                                                              |                                                     |
| <b>Test Certificates</b>                                                                                                                                   |                                                     |



#### Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:14IUH32AC>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/US/en/ps/US2:14IUH32AC>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:14IUH32AC&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:14IUH32AC&lang=en)

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/US2:14IUH32AC/certificate>



