

M12 female recept. A-cod. front incl. nut

TPE-wires 12x0.14 1m

Art.No.: 7000-19182-9790100

Weight: 0.084 kg

Country of origin: DE


Model designation: MSBFV-12E979_1.0

Flange female


M12, 12-pole

Front mounting

with multi-strand wire

[Link to Product](#)**Illustration**

1 >	BN	< 1
2 >	BU	< 2
3 >	WH	< 3
4 >	GN	< 4
5 >	PK	< 5
6 >	YE	< 6
7 >	BK	< 7
8 >	GY	< 8
9 >	RD	< 9
10 >	VT	< 10
11 >	GY PK	< 11
12 >	RD BU	< 12





Product may differ from Image



Header	
Cable length	1,00 m
Side 1	
Family construction form	M12
No. of poles	12
Coding	A
Mounting method	inserted, screwed
Threaded hole	M12 x 1
Tightening torque	0,6 Nm
Width across flats	SW14
Material	Zinc die-casting
Material contact	Copper alloy
Coating contact	gold plated
Degree of protection (EN IEC 60529)	IP67
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-19182-9790100
customs tariff number	85444290
EAN	4048879553667
Packaging unit	1
Electrical data Supply	
Operating voltage AC max.	30 V
Operating voltage DC max.	30 V
Current operating per contact max.	1,5 A
Diagnostics	
Status indication LED	no
Installation Connection	
Mounting set	M16 x 1.5
Width across flats	SW19
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67
Protection NEMA	6P, 4, 3

Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	0,8 kV
Material group (IEC 60664-1)	I

Mechanical data

Contour for corrugated hose	without
-----------------------------	---------

Mechanical data | Material data

Material housing	Zinc die-casting
Material screw connection	Zinc die-casting
Coating of fitting	nickel plated
Locking material	Zinc die-casting
Coating locking	Nickeled
Material gasket	FKM

Mechanical data | Mounting data

Mounting method	inserted, screwed
-----------------	-------------------

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Conformity

Product standard	EN IEC 61076-2-101 (M12)
------------------	--------------------------

Approvals

UL 50E	yes
--------	-----

Installation | Cable

Cable identification	979
Wire arrangement	brown, blue, white, green, pink, yellow, Black, gray, red, violet, gray-pink, red-blue
Cable weight	72 g/m
Material wire insulation	PP
Amount wires	12
Outer diameter insulation	1,25 mm
Conductor crosssection (wire)	0,14 mm ²
Operating temperature min. (static)	-40 °C
Operating temperature max. (static)	85 °C
Operating temperature min. (dynamic)	-25 °C
Operating temperature max. (dynamic)	85 °C
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	15 × Outer diameter