

Cable drum Ø 355mm

PVC 5x0.34 ye UL/CSA 100m

Art.No.: 7000-C0101-0150000


Weight: 6.404 kg

Country of origin: DE

Model designation: 100m Kabel 10080663(015)auf Spule 01

Cable drum (100 m)

PVC (UL/CSA)

5× 0.34 mm², yellow**Link to Product****Illustration**

Product may differ from Image

**Header**

Material short text

100m Kabel 10080663(015)auf Spule 01

Commercial data

URL Webshop

<https://shop.murrelektronik.com/7000-C0101-0150000>

GTIN	4048879339919
ECLASS-6.0	27062011
ECLASS-6.1	27061801
ECLASS-7.0	27061801
ECLASS-7.1	27061801
ECLASS-8.0	27061801
ECLASS-8.1	27061801
ECLASS-9.0	27061801
ECLASS-9.1	27061801
ECLASS-10.0.1	27061801
ECLASS-10.1	27061801
ECLASS-11.0	27061801
ECLASS-11.1	27061801
ECLASS-12.0	27061801
ECLASS-13.0	27061801
ECLASS-14.0	27061801
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444995
EAN	4048879339919
Packaging unit	1

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Installation | Cable

Cable identification	015
Cable Type	1
Amount stranding	1
Stranding	1 × 5 wires around core filler twisted
Filler	Yes
Wire arrangement	brown, black, blue, white, green-yellow
Cable weight	44 g/m
Material wire insulation	PVC
Amount wires	5
Outer diameter insulation	1,25 mm
Outer diameter tolerance core insulation	± 0,05 mm
Shore hardness wire insulation	45 5 Shore D
Material properties wire insulation	good machinability
Ingredient freeness wire insulation	lead-free, cadmium-free, CFC-free, silicone-free
Amount strands (wire)	19
Diameter of single wires	0,15 mm
Conductor crosssection (wire)	0,34 mm²
Material conductor wire	Stranded copper wire, bare
Conductor type (wire)	Strand class 5
Outer-diameter (jacket)	5,2 mm
Tolerance outer diameter (sheath)	± 5 %
Material jacket	PVC
Shore hardness jacket	85 5 Shore A
Freedom from ingredients (jacket)	lead-free, cadmium-free, CFC-free, silicone-free
Material property (jacket)	good machinability

Conductor resistance (wire)	57 Ω /km @ 20 °C
Nominal voltage max.	300 V
Withstand voltage (wire - wire)	2 kV @ 60 s
Withstand voltage (wire - jacket)	2 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity max. (wire)	4,5 A
Operating temperature min. (static)	-30 °C
Operating temperature max. (static)	80 °C
Operating temperature min. (dynamic)	-5 °C
Operating temperature max. (dynamic)	80 °C
Flame resistance	UL 1581 § 1080, CSA FT1, IEC 60332-1-2
Oil resistance	good
Chemical resistance	good
Other resistances	good resistance to gasoline
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter