

M12 Power female recept. K-cod. rear

PUR-wires 5x1.5 0.5m

Art.No.: 7000-P3295-9880050

Weight: 0.090 kg

Country of origin: DE

Model designation: MSWBKFH-U988_0.5

Flange female

M12, 5-pole

K-coded

Rear mounting

Power




with multi-strand wire




Fastening nut included in the delivery

Good chemical and oil resistance (oil resistance does not apply to use with PVC cable)

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)
Illustration




Product may differ from Image

**Header**

Material short text MSWBKFH-U988_0.5

Cable length 0,50 m

Side 1

Family construction form M12P

No. of poles 5

Coding K

Mounting method inserted, mounted

Threaded hole M12 x 1

Tightening torque 0,6 Nm

Width across flats SW17

Material contact Copper alloy

Coating contact gold plated

Degree of protection (EN IEC 60529) IP65, IP67, IP69K

Commercial dataURL Webshop <https://shop.murrelektronik.com/7000-P3295-9880050>

GTIN 4048879900553

ECCLASS-6.0	27279221
ECCLASS-6.1	27279220
ECCLASS-7.0	27440103
ECCLASS-7.1	27440103
ECCLASS-8.0	27440103
ECCLASS-8.1	27440103
ECCLASS-9.0	27440103
ECCLASS-9.1	27440109
ECCLASS-10.0.1	27440109
ECCLASS-10.1	27440103
ECCLASS-11.0	27440109
ECCLASS-11.1	27440103
ECCLASS-12.0	27440103
ECCLASS-13.0	27440109
ECCLASS-14.0	27440109
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444290
EAN	4048879900553
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	600 V
Current operating per contact max.	12 A

Diagnostics

Status indication LED	No
-----------------------	----

Installation | Connection

Mounting set	M16 x 1.5
Width across flats	SW19

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67, IP65
Protection NEMA	6P, 4, 3
Additional condition protection degree	mounted, screwed
Pollution Degree	3
Rated surge voltage	6 kV
Material group (IEC 60664-1)	I

Mechanical data

Contour for corrugated hose	without
-----------------------------	---------

Mechanical data | Material data

Material housing	Brass
Coating housing	nickel plated
Locking material	Brass
Coating locking	nickel plated
Material gasket	FKM

Mechanical data | Mounting data

Mounting method	inserted, screwed
-----------------	-------------------

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Conformity

Product standard	EN IEC 61076-2-111
------------------	--------------------

Approvals

UL 50E	Yes
--------	-----

Temperature range | Cable

Cable identification	988
Wire arrangement	brown, white, blue, black, green-yellow
Cable weight	97,5 g/m
Material wire insulation	PUR
Amount wires	5
Outer diameter insulation	2,4 mm
Amount strands (wire)	30
Diameter of single wires	0,25 mm
Conductor crosssection (wire)	1,5 mm ²
Material conductor wire	copper stranded wire, tinned
Conductor type (wire)	Strand class 5
Conductor resistance (wire)	13.3 Ω/km @ 20 °C
Nominal voltage max.	900 V
Withstand voltage (wire - wire)	3.31 kV
Withstand voltage (wire - jacket)	3.31 kV
Operating temperature min. (static)	-40 °C
Operating temperature max. (static)	90 °C
Operating temperature min. (dynamic)	-25 °C
Operating temperature max. (dynamic)	90 °C