

M23 female 0° 6-pole with cable

PVC 1.5 shielded or UL/CSA+drag ch. 10m

Art.No.: 7000-PS505-8651000

Weight: 1.287 kg

Country of origin: DE

Model designation: MS23PNBB6-552_865_10.0

Power cable for SINAMICS S120 and Motors with M23 connection

Female straight

M23, 6-pole




4-pole used

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

 Power cores: 12 A (1.5 mm²), 15 A (2.5 mm²); brake cores: 5 A (1.5 mm²)

[**Link to Product**](#)
Illustration




Product may differ from Image



Header

Material short text MS23PNBB6-552_865_10.0

Cable length 10,00 m

Side 1

Family construction form M23

Threaded hole M23 x 1

Tightening torque 2 Nm

Width across flats SW27

suitable for corrugated tube (internal Ø) 16 mm

Commercial data

URL Webshop <https://shop.murrelektronik.com/7000-PS505-8651000>

GTIN 4048879507288

ECLASS-6.0 27279218

ECLASS-6.1 27279218

ECLASS-7.0 27279218

ECLASS-7.1 27279218

ECLASS-8.0 27279218

ECLASS-8.1 27279218

ECLASS-9.0 27060327

ECLASS-9.1 27060311

ECLASS-10.0.1 27060311

ECLASS-10.1 27060311

ECLASS-11.0 27060311

ECLASS-11.1 27060311

ECLASS-12.0 27060327

ECLASS-13.0 27060311

ECLASS-14.0 27060311

ETIM-5.0 EC001855

ETIM-6.0 EC001855

ETIM-7.0 EC001855

ETIM-8.0 EC001855

customs tariff number 85444290

EAN 4048879507288

Packaging unit	1
Electrical data Supply	
Operating voltage AC max.	630 V
Operating voltage DC max.	630 V
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67, IP65
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	6 kV
Material group (IEC 60664-1)	I
Mechanical data Material data	
Material housing	PUR
Locking material	Brass
Coating locking	nickel plated
Mechanical data Mounting data	
Mounting method	inserted, screwed, Shaking protection
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality
Important installation notes	
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Installation Cable	
Cable identification	865
Function cable	Power
Stranding	1 x 4 wires stranded with filler
Cable shielding (type)	copper braid, tinned
Cable shielding (coverage)	85 %
Banding	Fiber tape, Fleece
Filler	Yes
Cable weight	117 g/m
Material wire insulation	TPM
Amount wires	4
Outer diameter insulation	2,4 mm
Outer diameter tolerance core insulation	± 0,1 mm
Ingredient freeness wire insulation	lead-free, CFC-free, silicone-free
Printing color of wire insulation	white (isolation black)
Amount strands (wire)	30
Diameter of single wires	0,25 mm
Conductor crosssection (wire)	1,5 mm ²
Material conductor wire	Stranded copper wire, bare
Conductor type (wire)	Strand class 5
Electrical function wire	Power
Outer-diameter (jacket)	8,1 mm
Tolerance outer diameter (sheath)	± 5 %
Material jacket	PVC
Freedom from ingredients (jacket)	lead-free, CFC-free, silicone-free
Conductor resistance (wire)	13.7 Ω/km @ 20 °C
Electrical capacity line constant (wire - wire)	150.000 pF/km
Electrical capacity line constant (wire - shield)	250.000 pF/km

Isolation resistance	5.000 MΩ × km
Max. rated voltage (conductor - ground)	600 V
Max. rated voltage (conductor - conductor)	1.000 V
Withstand voltage (wire - wire)	4 kV @ 300 s
Withstand voltage (wire - jacket)	4 kV @ 300 s
Withstand voltage (wire - shield)	4 kV @ 300 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity max. (wire)	14,4 A
Operating temperature min. (static)	-10 °C
Operating temperature max. (static)	80 °C
Operating temperature min. (dynamic)	-10 °C
Operating temperature max. (dynamic)	80 °C
Operating temperature min. (drag chain)	-10 °C
Operating temperature max. (drag chain)	80 °C
Flame resistance	IEC 60332-1-2
Oil resistance	UL 1581 @ 60°C, 168 h
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	18 × Outer diameter
No. of bending cycles (C-track)	0.1 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C
Travel speed (C-track)	0.5 m/s @ 25 °C
Acceleration (C-track)	2 m/s² @ 25 °C