

MVP12, 8XM12, 5POLE, PLUG. TERM.

W/o cap, with pot. separation, NPN-LED's

Art.No.: 276565

Weight: 0.120 kg

Country of origin: DE

Model designation: MVQ8-U-YH-NP-MP

8-way, 5-pole

Potential separation as option

with LED for digital NPN-signals 24 V DC




Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)

Illustration





Product may differ from Image



Header

Material short text MVQ8-U-YH-NP-MP

Commercial data

URL Webshop <https://shop.murrelektronik.com/276565>

GTIN 4048879061773

ECLASS-6.0 27279219

ECLASS-6.1 27279219

ECLASS-7.0 27279219

ECLASS-7.1 27279219

ECLASS-8.0 27279219

ECLASS-8.1 27279219

ECLASS-9.0 27440111

ECLASS-10.0.1 27440111

ECLASS-10.1 27440111

ECLASS-11.0 27440111

ECLASS-11.1 27440111

ECLASS-12.0 27440111

ECLASS-13.0 27440111

ECLASS-14.0 27440111

ETIM-5.0 EC002585

ETIM-6.0 EC002585

ETIM-7.0 EC002585

ETIM-8.0 EC002585

customs tariff number 85366990

EAN 4048879061773

Packaging unit 1

Electrical data | Supply

Operating voltage DC 24 V

Current operating per contact max. 4 A

Total current at 1 time current feed-in max. 8 A

Total current at 2 times current feed-in max. 16 A

Industrial Communication

Number of signals per port	2
----------------------------	---

Installation | Connection

Mounting set	M12 x 1
--------------	---------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	mounted, screwed

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	149,2 mm
Width	50,2 mm
Depth	16,5 mm
Mounting method	Schraubgewinde

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	80 °C

Connection type 2

Family construction form	Cap
No. of poles	21
Family construction form	M12
No. of poles	5
Coding	A
Gender	female
Color contact carrier	black
PIN 1	+
PIN 2	NC
PIN 3	-
PIN 4	S
PIN 5	PE