

MVP12, 8XM12, 5POLE, PLUG. TERM.

W/o cap, with pot. separation, w/o LED's

Art.No.: 276596

Weight: 0.094 kg

Country of origin: DE

Model designation: MVQ8-U-YH-XA-MP

8-way, 5-pole

Basic module without LED

Potential separation as option




Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)

Illustration





Product may differ from Image



Header

Material short text MVQ8-U-YH-XA-MP

Commercial data

URL Webshop <https://shop.murrelektronik.com/276596>

GTIN 4048879061667

ECLASS-6.0 27279219

ECLASS-6.1 27279219

ECLASS-7.0 27279219

ECLASS-7.1 27279219

ECLASS-8.0 27279219

ECLASS-8.1 27279219

ECLASS-9.0 27440111

ECLASS-10.0.1 27440111

ECLASS-10.1 27440111

ECLASS-11.0 27440111

ECLASS-11.1 27440111

ECLASS-12.0 27440111

ECLASS-13.0 27440111

ECLASS-14.0 27440111

ETIM-5.0 EC002585

ETIM-6.0 EC002585

ETIM-7.0 EC002585

ETIM-8.0 EC002585

customs tariff number 85366990

EAN 4048879061667

Packaging unit 1

Electrical data | Supply

Operating voltage DC 24 V

Current operating per contact max. 4 A

Total current at 1 time current feed-in max. 8 A

Total current at 2 times current feed-in max. 16 A

Industrial Communication

Number of signals per port	2
----------------------------	---

Installation | Connection

Mounting set	M12 x 1
--------------	---------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	mounted, screwed

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	149,2 mm
Width	50,2 mm
Depth	16,5 mm
Mounting method	Schraubgewinde

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	80 °C

Connection type 2

Family construction form	Cap
No. of poles	21
Family construction form	M12
No. of poles	5
Coding	A
Gender	female
Color contact carrier	black
PIN 1	+
PIN 2	NC
PIN 3	-
PIN 4	S
PIN 5	PE