

MIRO 6.2 PLUGGABLE PLUG IN MODULE INPUT RELAY

IN: 24 VDC - OUT: 250 VAC/DC / 6 A

Art.No.: 3000-16023-2100030
Weight: 0.010 kg
Country of origin: CZ
Model designation: Eingrel. 24V/230V 6A (Steckmodul)


Input relay
1 relay; 1 NO contact
Relay 24 V AC/DC
for MIRO 6.2 pluggable

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	Eingrel. 24V/230V 6A (Steckmodul)
Commercial data	
URL Webshop	https://shop.murrelektronik.com/3000-16023-2100030
GTIN	4048879021357
ECLASS-6.0	27371601
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601

ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879021357
Packaging unit	1

Electrical data | Input

Input voltage AC	24 V
Input voltage DC	24 V

Electrical data | Output

Switching voltage AC max.	250 V
Switching voltage DC max.	30 V
Switching current max.	6 A
Switching current DC	1 mA
Switching current DC min.	10 mA

Device protection | Electrical

Rated insulation voltage	300 V
--------------------------	-------

Mechanical data

Response time max.	5 ms
Drop-out time max.	6 ms

Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

Mechanical data | Mounting data

Height	15 mm
Width	5 mm
Depth	28 mm
Mounting method	inserted

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-40 °C