

Modlink MSDD-set: Frame 4000-68113-0000000,


insert 4000-68000-0910000

Art.No.: 4000-68113-0910000

Weight: 0.348 kg

Country of origin: CZ

Model designation: MSDD_1MV_2XUSB+RJ12,45_

[Link to Product](#)
Illustration


Product may differ from Image

Header

 Material short text **MSDD_1MV_2XUSB+RJ12,45_**
Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68113-0910000
GTIN	4048879036160
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806

ECCLASS-9.1	27189217
ECCLASS-10.0.1	27182806
ECCLASS-10.1	27182806
ECCLASS-11.0	27182806
ECCLASS-11.1	27182806
ECCLASS-12.0	27182806
ECCLASS-13.0	27182806
ECCLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879036160
Packaging unit	1

Frame

Material housing	Fine zinc die casting
Coating housing	surface finished
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

USB

USB specification	3.0
Looking techniques	Snap-in connector
Data transmission rate max.	5.000 Mbit/s
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	1,5 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V

RJ12

Family construction form	RJ12
Looking techniques	Snap-in connector
Family type Back side	RJ12
Operating voltage AC max.	48 V
Operating voltage DC max.	48 V
Operating current max.	1 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45

Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA