

### T-Coupler M12 male / 2x M12 female A-cod. F&B PRO

5-pol. / 2x 4-pol.

Art.No.: 7024-41131-0000000

Weight: 0.034 kg

Country of origin: PL

Model designation: T-Stück M12 St. 5pol./ 2x Bu. 4pol. F&B

T-coupler

F&B Pro

Male straight – females straight




M12, 5-pole – M12, 4-pole



Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

#### Illustration





Product may differ from Image

**Side 1**

Family construction form	M12
No. of poles	4
Coding	A
Gender	female
Mounting method	pluggable, screwed
Threaded hole	M12 x 1
Tightening torque	0,6 Nm
Width across flats	SW14
Degree of protection (EN IEC 60529)	IP67, IP69K, IP68, IP65

**Side 2**

Family construction form	M12
No. of poles	4
Coding	A
Gender	female
Mounting method	pluggable, screwed
Threaded hole	M12 x 1
Tightening torque	0,6 Nm
Width across flats	SW14
Degree of protection (EN IEC 60529)	IP67, IP69K, IP68, IP65

**Side 3**

Family construction form	M12
No. of poles	5
Coding	A
Gender	male
Mounting method	pluggable, screwed
Threaded hole	M12 x 1
Tightening torque	0,6 Nm
Width across flats	SW13
Degree of protection (EN IEC 60529)	IP67, IP69K, IP68, IP65

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/7024-41131-0000000">https://shop.murrelektronik.com/7024-41131-0000000</a>
customs tariff number	85366990

EAN	4048879871259
Packaging unit	1
<b>Electrical data   Supply</b>	
Operating voltage AC max.	60 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
<b>Diagnostics</b>	
Status indication LED	No
<b>Installation   Connection</b>	
Tightening torque	0,6 Nm
Mounting set	M12 x 1
Width across flats	SW 14
<b>Device protection   Electrical</b>	
Additional condition protection degree	inserted, screwed
<b>Mechanical data   Material data</b>	
Material housing	PP
Locking material	Stainless steel 1.4404 (V4A)
Material gasket	EPDM
<b>Mechanical data   Mounting data</b>	
Mounting method	inserted, screwed, Shaking protection
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-25 °C
Operating temperature max.	100 °C
<b>Important installation notes</b>	
Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
<b>Conformity</b>	
Product standard	EN IEC 61076-2-101 (M12)