

Modlink MSDD-set: Frame 4000-68123-0000000,

insert 4000-68000-0010000 + 4000-68000-1450000


Art.No.: 4000-68123-0011450

Weight: 0.754 kg

Country of origin: DE

Model designation: MSDD_2MV_VDE MIT LED_25B/S+RJ+USB

[Link to Product](#)**Illustration**



Product may differ from Image

Header

Material short text MSDD_2MV_VDE MIT LED_25B/S+RJ+USB

Commercial data

URL Webshop <https://shop.murrelektronik.com/4000-68123-0011450>

GTIN 4048879366809

ECLASS-6.0 27189217

ECLASS-6.1 27189217

ECLASS-7.0 27189217

ECLASS-7.1 27189217

ECLASS-8.0 27189217

ECLASS-8.1 27189217

ECLASS-9.0 27182806

ECLASS-9.1 27189217

ECLASS-10.0.1 27182806

ECLASS-10.1 27182806

ECLASS-11.0 27182806

ECLASS-11.1 27182806

ECLASS-12.0 27182806

ECLASS-13.0 27182806

ECLASS-14.0 27182806

ETIM-5.0 EC002625

ETIM-6.0 EC002625

ETIM-7.0 EC002625

ETIM-8.0 EC002625

customs tariff number 85366990

EAN 4048879366809

Packaging unit 1

customs tariff number 85366990

EAN 4048879366809

Packaging unit 1

Frame

Material housing Fine zinc die casting

Coating housing surface finished

Suitable for installation wall thickness min. 1 mm

Suitable for installation wall thickness max. 5 mm

Degree of protection (EN IEC 60529) IP65

Operating temperature min. -10 °C

Operating temperature max.	60 °C
Storage temperature min.	-25 °C

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

Germany (VDE)

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	Yes
Connection cross section max.	6 mm ²
AWG number max.	10
Operating voltage AC	250 V
Operating current	16 A
Status indication LED	yellow

USB

USB specification	2.0
Looking techniques	Snap-in connector
Data transmission rate max.	480 Mbit/s
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current max.	500 mA
Operating voltage DC (UL-listed)	42,4 V

SUB-D25

Family construction form	SUB-D25
Gender	Female
No. of poles	25
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D25
Gender Rear	male
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA