

**EOL - Modlink MSDD-set: Frame 4000-68123-0000000,**

discontinued - End of Life Date: 2024-12-31


Art.No.: 4000-68123-0141410

Weight: 0.668 kg

Country of origin: CZ

Model designation: X MSDD\_2MV\_VDE-OG.LED\_9BU/BU+RJ45\_

[Link to Product](#)**Illustration**



Product may differ from Image



| Commercial data                               |               |
|-----------------------------------------------|---------------|
| ECLASS-6.0                                    | 27189217      |
| ECLASS-6.1                                    | 27189217      |
| ECLASS-7.0                                    | 27189217      |
| ECLASS-8.0                                    | 27189217      |
| ECLASS-9.0                                    | 27182806      |
| ECLASS-10.1                                   | 27182806      |
| ECLASS-11.1                                   | 27182806      |
| ECLASS-12.0                                   | 27182806      |
| ETIM-5.0                                      | EC002625      |
| ETIM-6.0                                      | EC002625      |
| ETIM-7.0                                      | EC002625      |
| ETIM-8.0                                      | EC002625      |
| customs tariff number                         | 85389099      |
| customs tariff number                         | 85389099      |
| customs tariff number                         | 85389099      |
| customs tariff number                         | 85389099      |
| EAN                                           | 4048879034548 |
| EAN                                           | 4048879034548 |
| EAN                                           | 4048879034548 |
| EAN                                           | 4048879034548 |
| Packaging unit                                | 1             |
| Packaging unit                                | 1             |
| Packaging unit                                | 1             |
| Packaging unit                                | 1             |
| Frame                                         |               |
| Degree of protection (EN IEC 60529)           | IP65          |
| Operating temperature min.                    | -10 °C        |
| Operating temperature max.                    | 60 °C         |
| Storage temperature min.                      | -25 °C        |
| Storage temperature max.                      | 60 °C         |
| Suitable for installation wall thickness min. | 1 mm          |
| Suitable for installation wall thickness max. | 5 mm          |

|                                       |                                                |
|---------------------------------------|------------------------------------------------|
| Material housing                      | Fine zinc die casting                          |
| Coating housing                       | surface finished                               |
| <b>Shielding plate</b>                |                                                |
| Connection information                | Threaded hole M4                               |
| Tightening torque                     | 0,9 Nm                                         |
| <b>Germany (VDE)</b>                  |                                                |
| Connection cross section max.         | 2,5 mm <sup>2</sup>                            |
| AWG number max.                       | 14                                             |
| Operating voltage AC                  | 250 V                                          |
| Operating current min.                | 10 A                                           |
| Operating current max.                | 16 A                                           |
| Connection                            | Spring clamp terminals FK                      |
| No. of poles                          | 2 + PE                                         |
| Connections per pole                  | 2                                              |
| Protection contact present            | yes                                            |
| <b>SUB-D9</b>                         |                                                |
| Operating voltage AC                  | 48 V                                           |
| Operating voltage DC                  | 48 V                                           |
| Operating voltage AC max. (UL-listed) | 30 V                                           |
| Operating voltage DC max. (UL-listed) | 42,4 V                                         |
| Operating current                     | 3 A                                            |
| Current operating max. (UL)           | 175 mA                                         |
| Family construction form              | SUB-D9                                         |
| Family type Back side                 | SUB-D9                                         |
| Gender                                | female                                         |
| Gender Rear                           | female                                         |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles                          | 9                                              |
| <b>RJ45</b>                           |                                                |
| Operating voltage AC max. (UL-listed) | 30 V                                           |
| Operating voltage DC max. (UL-listed) | 42,4 V                                         |
| Current operating max. (UL)           | 175 mA                                         |
| Family construction form              | RJ45                                           |
| Family type Back side                 | RJ45                                           |
| Cable category min.                   | Cat5e                                          |
| Looking techniques                    | Snap-in connector                              |