

Modlight70 Pro connecting modul 8 pole M12

side, with magnet base

Art.No.: 4000-76070-1500002
Weight: 0.530 kg
Country of origin: CZ
Model designation: Modlight70 Pro BASE M12-8S MAGNET


Basic
with M12 connection
with magnet base
M12 (8-pole), sideways
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	Modlight70 Pro BASE M12-8S MAGNET
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-76070-1500002
GTIN	4048879759601
ECLASS-6.0	27371232
ECLASS-6.1	27371232
ECLASS-7.0	27371232
ECLASS-7.1	27371232
ECLASS-8.0	27371232
ECLASS-8.1	27371232
ECLASS-9.0	27371232
ECLASS-9.1	27371232
ECLASS-10.0.1	27371232
ECLASS-10.1	27371232
ECLASS-11.0	27371232
ECLASS-11.1	27371232

ECLASS-12.0	27371232
ECLASS-13.0	27371232
ECLASS-14.0	27371232
ETIM-5.0	EC001152
ETIM-6.0	EC001152
ETIM-7.0	EC001152
ETIM-8.0	EC001152
customs tariff number	85319000
EAN	4048879759601
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted

Mechanical data

Adhesive force	290 N
----------------	-------

Mechanical data | Material data

Material housing	Plastic
Color housing	black

Mechanical data | Mounting data

Height	135 mm
Width	88 mm
Depth	70 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	60 °C

Connection type 1

Family construction form	M12
No. of poles	8
Coding	A
Gender	male
PIN 1	24 V DC / 0 V
PIN 2	LED-Modul RD
PIN 3	0 V / 24 V DC
PIN 4	LED-Modul CL
PIN 5	LED-Modul YE
PIN 6	LED-Modul BU
PIN 7	LED-Modul GN
PIN 8	Buzzer