

MPUUW ANALOG COUPLER COMPONENT

IN: 0..10 V - OUT: 0..10 V / 300 mA

Art.No.: 44201

Weight: 0.171 kg

Country of origin: CZ

Model designation: MPUUW 44 201

INPUT: 0...10 V DC



OUTPUT: 0...10 V DC, 300 mA

Screw terminals

This product is a processing component and must only be used by authorized manufacturers or people.
Input and output galvanically separated

Link to Product

Illustration



Product may differ from Image



Header

Material short text

MPUUW 44 201

Commercial data

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-02-13

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

URL Webshop	https://shop.murrelektronik.com/44201
GTIN	4048879028516
ECLASS-6.0	27210990
ECLASS-6.1	27210901
ECLASS-7.0	27210901
ECLASS-7.1	27210901
ECLASS-8.0	27210901
ECLASS-8.1	27210901
ECLASS-9.0	27210901
ECLASS-9.1	27210901
ECLASS-10.0.1	27210901
ECLASS-10.1	27210901
ECLASS-11.0	27210901
ECLASS-11.1	27210901
ECLASS-12.0	27210901
ECLASS-13.0	27210901
ECLASS-14.0	27210901
ETIM-5.0	EC002477
ETIM-6.0	EC002477
ETIM-7.0	EC002477
ETIM-8.0	EC002477
customs tariff number	85437090
EAN	4048879028516
Packaging unit	1
Electrical data	
Accuracy (of full scale)	0,5 %
Electrical data Supply	
Operating voltage DC	24 V
Operating voltage DC min.	19,2 V
Operating voltage DC max.	28,8 V
Operating current max.	300 mA
Electrical data Input	
Input resistor	10 k Ω
Electrical data Output	
Output current max.	0,3 A
Industrial Communication	
Transmission frequency max.	1.000 Hz
Mechanical data Mounting data	
Height	62 mm
Width	43 mm
Depth	67,5 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	50 °C
Connection type 2	
Connection type 1	Input / Output
Family construction form	terminal
No. of poles	5
Gender	female

Connection	Screw terminals SK
PIN 1	+
PIN 2	+
PIN 3	-
PIN 4	-
PIN 5	In
Family construction form	terminal
No. of poles	5
Gender	female
Connection	Screw terminals SK
PIN 1	+
PIN 2	+
PIN 3	-
PIN 4	-
PIN 5	OUT