

RMMDUE 11/24 DC INPUT RELAY

IN: 24 VDC - OUT: 250 VAC/DC / 6 A

Art.No.: 51130

Weight: 0.038 kg

Country of origin: CZ

Model designation: RMMDUE 11/24 DC



1 relay; 1 NO/NC contact

5 A

24 V DC

with minus plug link

When the max. switching voltage/current is exceeded the gold plating is destroyed. Max. current is then 5 A.

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

RMMDUE 11/24 DC

Commercial data

The information in this Product-PDF has been compiled with the utmost care.
 Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-02-09

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

URL Webshop	https://shop.murrelektronik.com/51130
GTIN	4048879027755
Scope of delivery	Jumper (Art-No. 90960)
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879027755
Packaging unit	1

Electrical data | Input

Input voltage DC	24 V
Input voltage DC min.	19,2 V
Input voltage DC max.	30 V
Input current	17 mA

Electrical data | Output

Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	5 A
Switching current DC	1 mA
Switching frequency max.	15 Hz
Power rating AC max.	1.500 VA
Power rating DC max.	180 W
Switching capacity AC-12 (EN IEC 60947-5-1)	5 A (24/110/230 V AC)
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V 3 A @ 110 V 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1.3 A @ 24 V 0.25 A @ 110 V 0.1 A @ 230 V

Diagnostics

Status indication LED	yellow
-----------------------	--------

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	4 kV

Device protection | Mechanical

Mechanical endurance	0 cycles
----------------------	----------

Mechanical data

Response time max.	10 ms
Drop-out time max.	10 ms
Bounce time max.	1 ms

Mechanical data | Material data

Material contact	Ag hv, Ag Ni 0.15 hv
------------------	----------------------

Mechanical data | Mounting data

Height	82 mm
Width	12 mm
Depth	68 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715), G32

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C

Connection type 2

Connection type 1	X1
Connection type 2	X2
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	- A 2
PIN 2	+ A 1
Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	11
PIN 2	14
PIN 3	11
PIN 4	12