

RMMD-2A/24VDC INPUT RELAY

IN: 24 VDC - OUT: 250 VAC/DC / 2 A

Art.No.: 51140

Weight: 0.041 kg

Country of origin: CZ

Model designation: RMMD-2A/24VDC



1 relay; 2 NO contacts

2 A

24 V DC

Screw terminals

with minus plug link

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

RMMD-2A/24VDC

Commercial data

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-02-10

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

URL Webshop	https://shop.murrelektronik.com/51140
GTIN	4048879027731
Scope of delivery	Jumper (Art-No. 90960)
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879027731
Packaging unit	1

Electrical data | Input

Input voltage DC	24 V
Input voltage DC min.	19,2 V
Input voltage DC max.	30 V
Input current	15 mA

Electrical data | Output

Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	2 A
Switching current DC min.	0,1 mA
Switching frequency max.	15 Hz
Power rating AC max.	125 VA
Power rating DC max.	60 W
Switching capacity AC-12 (EN IEC 60947-5-1)	2 A (24/110/230 V AC)
Switching capacity AC-15 (EN IEC 60947-5-1)	1 A (24 V AC); 0.1 A (230 V AC)
Utilization category DC-13 (EN IEC 60947-5-1)	0.8 A @ 24 V 0.1 A @ 110 V 0.01 A @ 230 V

Diagnostics

Status indication LED	yellow
-----------------------	--------

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	1,5 kV

Device protection | Mechanical

Mechanical endurance	0 cycles
----------------------	----------

Mechanical data

Response time max.	10 ms
--------------------	-------

Drop-out time max.	10 ms
--------------------	-------

Bounce time max.	1 ms
------------------	------

Mechanical data | Material data

Material contact	Ag Au
------------------	-------

Mechanical data | Mounting data

Height	82 mm
--------	-------

Width	12 mm
-------	-------

Depth	68 mm
-------	-------

Mounting method	geschnappt
-----------------	------------

Suitable for mounting type	Mounting rail TH35, (EN 60715), G32
----------------------------	-------------------------------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Connection type 3

Family construction form	terminal
--------------------------	----------

No. of poles	2
--------------	---

Gender	female
--------	--------

Connection	Screw terminals SK
------------	--------------------

PIN 1	14
-------	----

PIN 2	24
-------	----

Family construction form	terminal
--------------------------	----------

No. of poles	2
--------------	---

Gender	female
--------	--------

Connection	Screw terminals SK
------------	--------------------

PIN 1	13
-------	----

PIN 2	23
-------	----

Family construction form	terminal
--------------------------	----------

No. of poles	2
--------------	---

Gender	female
--------	--------

Connection	Screw terminals SK
------------	--------------------

PIN 1	+ A 1
-------	-------

PIN 2	- A 2
-------	-------