

RM 14/230V AC OUTPUT RELAY

IN: 230 VAC/DC - OUT: 250 VAC/DC / 2 A

Art.No.: 51413

Weight: 0.098

Country of origin: CZ



Model designation: RM 14/230V AC KL.BZ.N.EN

1 relay; 4 NO/NC contacts

2 A

230 V AC

Screw terminals

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

RM 14/230V AC KL.BZ.N.EN

Commercial data

URL Webshop	https://shop.murrelektronik.com/51413
GTIN	4048879027625
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879027625
Packaging unit	1

Electrical data | Input

Input voltage AC	230 V
Input voltage AC min.	195 V
Input voltage AC max.	250 V
Input voltage DC	230 V
Input voltage DC min.	195 V
Input voltage DC max.	250 V
Input current	10 mA

Electrical data | Output

Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	2 A
Switching current DC	0.1 mA
Switching frequency max.	0.1 Hz
Additional condition switching frequency	with load
Power rating AC max.	125 VA
Power rating DC max.	60 W
Switching capacity AC-12 (EN IEC 60947-5-1)	2 A (24 V AC); 0.5 A (230 V AC)
Switching capacity AC-15 (EN IEC 60947-5-1)	1 A (24 V AC); 0.1 A (230 V AC)
Utilization category DC-13 (EN IEC 60947-5-1)	0.8 A @ 24 V 0.01 A @ 230 V

Diagnostics

Status indication LED	red
-----------------------	-----

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	1.5 kV

Device protection | Mechanical

Mechanical endurance 0 cycles

Mechanical data

Response time max. 10 ms
 Drop-out time max. 20 ms
 Bounce time max. 2 ms

Mechanical data | Material data

Material contact Ag Au

Mechanical data | Mounting data

Height 75 mm
 Width 22.5 mm
 Depth 102 mm
 Mounting method geschnappt
 Suitable for mounting type Mounting rail TH35, (EN 60715), G32

Environmental characteristics | Climatic

Operating temperature min. -20 °C
 Operating temperature max. 55 °C

Connection type 4

Family construction form	terminal
No. of poles	3
Gender	female
Connection	Screw terminals SK
PIN 1	12
PIN 2	11
PIN 3	14
Family construction form	terminal
No. of poles	3
Gender	female
Connection	Screw terminals SK
PIN 1	31
PIN 2	32
PIN 3	34
Family construction form	terminal
No. of poles	4
Gender	female
Connection	Screw terminals SK
PIN 1	21
PIN 2	24
PIN 3	22
PIN 4	41
Family construction form	terminal
No. of poles	4
Gender	female
Connection	Screw terminals SK
PIN 1	A 1
PIN 2	A 2
PIN 3	44
PIN 4	42