

RMM 24VDC OUTPUT RELAY

IN: 24 VDC - OUT: 250 VAC/DC / 6 A

Art.No.: 51507

Weight: 0.029 kg

Country of origin: CZ



Model designation: RMM 11/24 DC

1 relay; 1 NO contact

6 A

24 V DC

Screw terminals

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

RMM 11/24 DC

Commercial data

URL Webshop	https://shop.murrelektronik.com/51507
GTIN	4048879027571
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879027571
Packaging unit	1

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Input voltage AC	24 V
Input voltage AC min.	19,2 V
Input voltage AC max.	30 V
Input voltage DC	24 V
Input voltage DC min.	19,2 V
Input voltage DC max.	30 V
Input current	15 mA

Electrical data | Output

Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	6 A
Switching current DC	100 mA
Power rating AC max.	1.250 VA
Power rating DC max.	240 W
Switching capacity AC-12 (EN IEC 60947-5-1)	6 A (24/110/230 V AC)
Utilization category AC-15 (EN IEC 60947-5-1)	4 A @ 24 V 4 A @ 110 V 4 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V 0.25 A @ 110 V 0.1 A @ 230 V

Diagnostics

Status indication LED	red
-----------------------	-----

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	4 kV

Device protection | Mechanical

Mechanical endurance	0 cycles
----------------------	----------

Mechanical data | Material data

Material contact	Ag Ni
------------------	-------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	60 °C

Connection type 2

Family construction form	terminal
No. of poles	2
Gender	female
Connection	Screw terminals SK
PIN 1	13
PIN 2	14
Family construction form	terminal
No. of poles	2
Gender	female
Connection	Screw terminals SK
PIN 1	- A 1
PIN 2	+ A 2