

RMM 11/24VDC WITH GROUND BRIDGE OUTPUT RELAY

IN: 24 VAC/DC - OUT: 250 VAC/DC / 5 A

Art.No.: 51851

Weight: 0.031 kg

Country of origin: CZ

Model designation: RMM 11/24VDC M.SCH.MASSE



1 relay; 1 NO contact

5 A

24 V AC/DC

with minus plug link

Screw terminals

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

RMM 11/24VDC M.SCH.MASSE

Commercial data

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-02-10

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

URL Webshop	https://shop.murrelektronik.com/51851
GTIN	4048879027342
Scope of delivery	Jumper (Art-No. 90960)
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879027342
Packaging unit	1

Electrical data | Input

Input voltage AC	24 V
Input voltage AC min.	19,2 V
Input voltage AC max.	30 V
Input voltage DC	24 V
Input voltage DC min.	19,2 V
Input voltage DC max.	30 V
Input current	15 mA

Electrical data | Output

Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	5 A
Switching current DC	100 mA
Switching frequency max.	10 Hz
Power rating AC max.	1.250 VA
Power rating DC max.	240 W
Switching capacity AC-12 (EN IEC 60947-5-1)	5 A (24/110/230 V AC)
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V 3 A @ 110 V 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1.5 A @ 24 V 0.3 A @ 110 V 0.15 A @ 230 V

Diagnostics

Status indication LED	red
-----------------------	-----

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	4 kV

Device protection | Mechanical

Mechanical endurance 0 cycles

Mechanical data

Response time max. 10 ms
 Drop-out time max. 15 ms
 Bounce time max. 1,5 ms

Mechanical data | Material data

Material contact Ag Ni 0.15 hv

Mechanical data | Mounting data

Height 56 mm
 Width 12 mm
 Depth 65 mm
 Mounting method geschnappt
 Suitable for mounting type Mounting rail TH35, (EN 60715), G32

Environmental characteristics | Climatic

Operating temperature min. -25 °C
 Operating temperature max. 60 °C
 Ambient temperature (storage, transport) -40 °C ... 80 °C

Connection type 2

Connection type 1 X1
 Connection type 2 X2
 Family construction form terminal
 No. of poles 2
 Gender female
 Color contact carrier green
 Connection Screw terminals SK
 PIN 1 A 2
 PIN 2 A 1
 Family construction form terminal
 No. of poles 2
 Gender female
 Color contact carrier green
 Connection Screw terminals SK
 PIN 1 13
 PIN 2 14