

## POTENTIAL TERMINAL BLOCK GRAY GRAY BR BL

Art.No.: 56078  
 Weight: 0.079 kg  
 Country of origin: CZ  
 Model designation: Potenzialkbl. grau grau braun blau


Potential terminal block  
 gray/gray/brown/blue

### Link to Product

#### Illustration



Product may differ from Image



#### Header

Material short text Potenzialkbl. grau grau braun blau

#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/56078">https://shop.murrelektronik.com/56078</a>
GTIN	4048879049467
ECLASS-6.0	27141106
ECLASS-6.1	27141106
ECLASS-7.0	27141106
ECLASS-7.1	27141106
ECLASS-8.0	27141106
ECLASS-8.1	27141106
ECLASS-9.0	27141106
ECLASS-9.1	27141106
ECLASS-10.0.1	27141106
ECLASS-10.1	27141106
ECLASS-11.0	27141106
ECLASS-11.1	27141106
ECLASS-12.0	27141106
ECLASS-13.0	27141106
ECLASS-14.0	27141106
ETIM-5.0	EC001283
ETIM-6.0	EC001283

ETIM-7.0	EC001283
ETIM-8.0	EC001283
customs tariff number	85369010
EAN	4048879049467
Packaging unit	1

**Electrical data | Supply**

Operating voltage AC max.	30 V
Operating voltage DC max.	30 V
Total current max.	10 A

**Installation**

Connection cross section max.	2,5 mm <sup>2</sup>
AWG number min.	28
AWG number max.	14

**Installation | Connection**

Connection	Spring clamp plug-in terminals
------------	--------------------------------

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

**Mechanical data | Mounting data**

Height	70 mm
Width	56 mm
Depth	32,5 mm

**Environmental characteristics | Climatic**

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Ambient temperature (storage, transport)	-40 °C ... 85 °C