

EOL - Gateway CC-Link/AS-i, 1 Master, P24

discontinued - End of Life Date: 2024-12-31

Art.No.: 56473
Weight: 0.500 kg
Country of origin: DE
Model designation: X Gateway CC/AS-i-24, 1 Master 3.0 IP20


AS-Interface/CC-Link
Power 24V
Specification 3.0
Current manuals, GSD/type data can be downloaded at: www.murrelektronik.com
Other gateways on request.
Gateway-Singlemaster
AS-Interface data decoupling integrated
AS-Interface duplicate address detection
AS-Interface EMC detector integrated

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27242608
ECLASS-6.1	27242608
ECLASS-7.0	27242608
ECLASS-8.0	27242608
ECLASS-9.0	27242608
ECLASS-10.1	27242608
ECLASS-11.1	27242608
ECLASS-12.0	27242608
ETIM-5.0	EC001604
ETIM-6.0	EC001604
ETIM-7.0	EC001604
ETIM-8.0	EC001604
customs tariff number	85176200

customs tariff number	85176200
EAN	4048879661683
EAN	4048879661683
Packaging unit	1
Packaging unit	1

Electrical data

Rated operating current AS-Interface max.	250 mA
Security level	PELV

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	20 V
Operating voltage DC max.	30,6 V

Industrial communication

Supported protocol	CC-Link
--------------------	---------

Industrial communication | Bus data

Automatic baudrate detection	no
Baud rate min.	156 kBaud
Baud rate max.	10 MBaud

Industrial communication | AS-Interface

AS-i specification	V3.0
Number of slaves max.	62
Diagnostic interface serial	None
Cycle time AS-i	150 µs × (number of slaves + 2)

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Rated insulation voltage	500 V

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	120 mm
Width	85 mm
Depth	83 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C

Conformity

Product standard	EN 61131-2, EN 62026-2
------------------	------------------------