

Cube67 Diagnostic Gateway

Diagnosis made easy, Simple system overview

Art.No.: 56968

Weight: 0.915 kg

Country of origin: DE

Model designation: Cube67 Diagnose Gateway



Cube67


Diagnostic gateway

Ethernet TCP/IP

[Link to Product](#)

Illustration





Product may differ from Image



Header	
Material short text	Cube67 Diagnose Gateway
Commercial data	
URL Webshop	https://shop.murrelektronik.com/56968
GTIN	4048879652216
ECLASS-6.0	27242608
ECLASS-6.1	27242608
ECLASS-7.0	27242608
ECLASS-7.1	27242608
ECLASS-8.0	27242608
ECLASS-8.1	27242608
ECLASS-9.0	27242608
ECLASS-9.1	27242608
ECLASS-10.0.1	27242608
ECLASS-10.1	27242608
ECLASS-11.0	27242608
ECLASS-11.1	27242608
ECLASS-12.0	27242608
ECLASS-13.0	27242608
ECLASS-14.0	27242608
ETIM-5.0	EC001604
ETIM-6.0	EC001604
ETIM-7.0	EC001604
ETIM-8.0	EC001604
customs tariff number	85389099
EAN	4048879652216
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Current consumption max.	200 mA
Industrial communication Bus data	

Internal system connection Yes

Device protection | Electrical

Degree of protection (EN IEC 60529) IP67
 Invers-polarity protection Yes
 Over voltage protection Yes

Mechanical data | Mounting data

Height 42 mm
 Width 63 mm
 Depth 225 mm
 Suitable for mounting type 2-hole screw mounting

Environmental characteristics | Climatic

Operating temperature min. 0 °C
 Operating temperature max. 55 °C
 Ambient temperature (storage, transport) -25 °C ... 70 °C

Connection type 4

Connection type 1	Bus Out
Connection type 2	Port1, Port2
Connection type 3	Power In
Connection type 4	Power Out
Family construction form	M12
No. of poles	6
Coding	A
Gender	female
Color contact carrier	black
PIN 1	24 V DC (UA)
PIN 2	24 V DC (US)
PIN 3	0 V
PIN 4	Bus internal
PIN 5	Bus internal
PIN 6	0 V
Family construction form	M12
No. of poles	4
Coding	D
Gender	female
Color contact carrier	black
Mounting method	inserted, screwed
Tightening torque	0,6 Nm
PIN 1	TD +
PIN 2	RD +
PIN 3	TD -
PIN 4	RD -
PIN 5	n.c.
Family construction form	7/8"
No. of poles	5
Gender	male
Color contact carrier	black
PIN 1	0 V
PIN 2	0 V
PIN 3	PE
PIN 4	24 V DC (US)
PIN 5	24 V DC (UA)
Family construction form	7/8"
No. of poles	5

Gender	female
Color contact carrier	black
PIN 1	0 V
PIN 2	0 V
PIN 3	PE
PIN 4	24 V DC (US)
PIN 5	24 V DC (UA)