

CUBE20S POWER MODULE

24VDC

Art.No.: 57130

Weight: 0.074 kg

Country of origin: TH

Model designation: Cube20S Power module 24VDC


Power module
Expansion module
for external voltage supply

Link to Product

Illustration



Product may differ from Image



Header

Material short text Cube20S Power module 24VDC

Commercial data

URL Webshop	https://shop.murrelektronik.com/57130
GTIN	4048879422888
ECLASS-6.0	27242610
ECLASS-6.1	27242611
ECLASS-7.0	27242611
ECLASS-7.1	27242611
ECLASS-8.0	27242611
ECLASS-8.1	27242611
ECLASS-9.0	27242611
ECLASS-9.1	27242611
ECLASS-10.0.1	27242611
ECLASS-10.1	27242611
ECLASS-11.0	27242611
ECLASS-11.1	27242611
ECLASS-12.0	27242611
ECLASS-13.0	27242611

ECLASS-14.0	27242611
ETIM-5.0	EC001600
ETIM-6.0	EC001600
ETIM-7.0	EC001600
ETIM-8.0	EC001600
customs tariff number	85369010
EAN	4048879422888
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Total current max.	10 A
Electrical data Input	
Input voltage DC	24 V
Input voltage DC min.	20,4 V
Input voltage DC max.	28,8 V
Electrical data Output	
Output voltage DC	24 V
Output current	10 A
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Height	109 mm
Width	12,9 mm
Depth	76,5 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-25 °C
Connection type 1	
Connection type 1	Power
Family construction form	terminal
No. of poles	8
Gender	female
Connection	Spring clamp terminals FK
PIN 1	n.c.
PIN 2	24 V DC
PIN 3	0 V
PIN 4	24 V DC Sys
PIN 5	n.c.
PIN 6	24 V DC
PIN 7	0 V
PIN 8	0 V Sys