

Xelity 6TX Unmanaged Switch 6 Port 100Mbit

Art.No.: 58811

Weight: 0.139 kg

Country of origin: DE


Model designation: Xelity 6TX

6 port unmanaged switch

Connection cables are in the online shop under "Connection Technology".

[Link to Product](#)

Illustration



Product may differ from Image



Header

Material short text Xelity 6TX

Commercial data

URL Webshop <https://shop.murrelektronik.com/58811>

GTIN 4048879798396

ECLASS-6.0 19170106

ECLASS-6.1 19170106

ECLASS-7.0 19170106

ECLASS-7.1 19170106

ECLASS-8.0 19170106

ECLASS-8.1 19170106

ECLASS-9.0 19170402

ECLASS-9.1 19170106

ECLASS-10.0.1 19170402

ECLASS-10.1 19170402

ECLASS-11.0 19170402

ECLASS-11.1 19170402

ECLASS-12.0 19170402

ECLASS-13.0 19170402

ECLASS-14.0 19170402

ETIM-5.0 EC000734

ETIM-6.0 EC000734

ETIM-7.0	EC000734
ETIM-8.0	EC000734
customs tariff number	85176200
EAN	4048879798396
Packaging unit	1
Electrical data Supply	
Operating voltage DC min.	9,5 V
Operating voltage DC max.	31,5 V
Industrial Communication	
Data transmission rate max.	100 Mbit/s
Industrial communication Ethernet functionality	
VLAN unmanaged (IEEE 802.1Q)	Yes
Switch type	unmanaged
duplex	Full duplex
Auto-negotiation	Yes
Auto-crossover	Yes
Diagnostics	
Alarm contact	No
Diagnostic	No voltage
LED display	Ethernet connection/data traffic
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Invers-polarity protection	Yes
Over voltage protection	Yes
Mechanical data Material data	
Material housing	Plastic
Color housing	black
Mechanical data Mounting data	
Height	140 mm
Width	30 mm
Depth	85,1 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-40 °C
Connection type 2	
Connection type 1	6
Family construction form	RJ45
No. of poles	8
Gender	female
Color contact carrier	black
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.

Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	24 V DC (UB 1)
PIN 2	0 V
PIN 3	PE
PIN 4	n.c.