

6 TX managed switch with Gigabit

+ 4 power M12 IP67

Art.No.: 58860

Weight: 0.966 kg

Country of origin: DE

Model designation: 6 TX M GE + 4 Power M12 IP67

6-port managed IP 67 gigabit switch, 4 power ports

6 Gigabit ports

4 power ports, A-coded


Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



Header

Material short text 6 TX M GE + 4 Power M12 IP67

Commercial data

URL Webshop	https://shop.murrelektronik.com/58860
GTIN	4048879852289
ECLASS-11.1	19170401
customs tariff number	85176200
EAN	4048879852289
Packaging unit	1

Electrical data | Supply

Operating voltage DC min.	18 V
Operating voltage DC max.	28 V

Industrial Communication

Data transmission rate max.	2.500 Mbit/s
-----------------------------	--------------

Industrial communication | Ethernet functionality

LLDP frames	forwarding
Switch type	managed

duplex	Full duplex
Auto-negotiation	Yes
Auto-crossover	Yes
Ring topology	STP, RSTP

Industrial communication | IIoT functions

Webserver	HTTP, HTTPS
-----------	-------------

Switch Management

NAT	1:1
VLAN managed (IEEE 802.1Q)	Yes
VLANs max. (IEEE 802.1Q)	64
RSTP (IEEE 802.1D-2004, IEC 62439-1)	Default on
Simple Network Management Protocol (SNMP)	v1 + v2c + v3 (default active)
Time synchronization	NTP client
Addressing	SSH-Befehlszeile, DCP, BOOTP/DHCP client

Diagnostics

Alarm contact	No
Diagnostic	No voltage
LED display	Ethernet connection/data traffic
RMON	Yes
Port mirroring	1:1
Remote maintenance	Open VPN client
Syslog	Yes
SNMP traps	Yes

Installation | Connection

Number ports	6
--------------	---

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data | Material data

Material housing	Metal
------------------	-------

Mechanical data | Mounting data

Height	225 mm
Width	63 mm
Depth	42 mm
Suitable for mounting type	2-hole screw mounting

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	45 °C