

MIRO 12.4 24V-2U OUTPUT RELAY

IN: 24 VAC/DC - OUT: 250 VAC/DC / 6 A

Art.No.: 6652103

Weight: 0.046 kg

Country of origin: CZ

Model designation: MIRO12,4-1AUSG.REL.24V-2U-FK




2 NO/NC contacts


6 A

24 V AC/DC

Spring clamp terminals

safe separation (EN 60947-1)

[Link to Product](#)**Illustration**



Product may differ from Image



Header	
Material short text	MIRO12,4-1AUSG.REL.24V-2U-FK
Commercial data	
URL Webshop	https://shop.murrelektronik.com/6652103
GTIN	4048879022071
ECLASS-6.0	27371601
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879022071
Packaging unit	1
Electrical data Input	
Input voltage AC	24 V
Input voltage AC min.	19,2 V
Input voltage AC max.	30 V
Input voltage DC	24 V
Input voltage DC min.	19,2 V

Input voltage DC max.	30 V
Input current	20 mA
Electrical data Output	
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	6 A
Switching current DC	100 mA
Switching frequency max.	10 Hz
Power rating AC max.	1.500 VA
Power rating DC max.	120 W
Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24 V 6 A @ 110 V 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V 3 A @ 110 V 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V 0.2 A @ 110 V 0.1 A @ 230 V
Diagnostics	
Status indication LED	green
Device protection	
Condition lifetime	load-dependent
Device protection Electrical	
Electrical lifetime	0 cycles
Rated surge voltage	4 kV
Device protection Mechanical	
Mechanical endurance	0 cycles
Mechanical data	
Response time max.	10 ms
Drop-out time max.	15 ms
Bounce time max.	1,5 ms
Mechanical data Material data	
Material contact	Ag Sn O ₂
Mechanical data Mounting data	
Height	90 mm
Width	12,4 mm
Depth	65 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C