

MIRO OFF-DELAY ZEITRELAY 24VDC-1S**MIRO 6.2 TIMER OFF-DELAY**

Art.No.: 6652310

Weight: 0.035 kg

Country of origin: CZ




Model designation: MIRO OFF-DELAY ZEITRELAIS 24VDC-1S



Relay output

Switch-off delay: 0.1...10 s

Spring clamp terminals

safe separation (EN 60947-1)

[Link to Product](#)**Illustration**



Product may differ from Image



Header

Material short textMIRO OFF-DELAY ZEITRELAIS 24VDC-1S

Commercial data

URL Webshop	https://shop.murrelektronik.com/6652310
GTIN	4048879021937
ECLASS-6.0	27371790
ECLASS-6.1	27371790
ECLASS-7.0	27371790
ECLASS-7.1	27371790
ECLASS-8.0	27371605
ECLASS-8.1	27371605
ECLASS-9.0	27371605
ECLASS-9.1	27371605
ECLASS-10.0.1	27371605
ECLASS-10.1	27371605
ECLASS-11.0	27371605
ECLASS-11.1	27371605
ECLASS-12.0	27371605
ECLASS-13.0	27371605
ECLASS-14.0	27371605
ETIM-5.0	EC001439
ETIM-6.0	EC001439
ETIM-7.0	EC001439
ETIM-8.0	EC001439
customs tariff number	85364900
EAN	4048879021937
Packaging unit	1

Electrical data | Input

Input voltage DC	24 V
Input voltage DC min.	20,4 V
Input voltage DC max.	26,4 V
Input current	20 mA
Input current DC max.	10 mA

Control voltage DC	24 V
Control voltage DC min.	20,4 V
Control voltage DC max.	26,4 V
Control current	5 mA

Electrical data | Output

Output voltage adjustable	No
Output current max.	6 A
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	100 mA
Switching frequency max.	10 Hz
Power rating AC max.	1.500 VA
Power rating DC max.	120 W
Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24 V 6 A @ 110 V 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V 3 A @ 110 V 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V 0.2 A @ 110 V 0.1 A @ 230 V

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	4 kV

Device protection | Mechanical

Mechanical endurance	0 cycles
----------------------	----------

Mechanical data

Response time max.	10 ms
Drop-out time max.	15 ms
Bounce time max.	1,5 ms

Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

Mechanical data | Mounting data

Height	91 mm
Width	6,2 mm
Depth	70 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C

Connection type 5

Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	+ A 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	18

Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	17
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	+ B 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	- A 2