

## MIRO 6.2 OPTO-COUPLER MODULE

IN: 53 VDC - OUT: 48 VDC / 6 A

Art.No.: 6652519

Weight: 0.030 kg

Country of origin: CZ

Model designation: MIRO,TR,24VDC,24VDC,6A, FK



Transistor 6 A

24 V DC

Spring clamp terminals

### Link to Product

#### Illustration



Product may differ from Image



#### Header

Material short text

MIRO,TR,24VDC,24VDC,6A, FK

#### Commercial data

URL Webshop

<https://shop.murrelektronik.com/6652519>

GTIN	4048879021753
ECLASS-6.0	27371601
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-7.1	27371604
ECLASS-8.0	27371604
ECLASS-8.1	27371604
ECLASS-9.0	27371604
ECLASS-9.1	27371604
ECLASS-10.0.1	27371604
ECLASS-10.1	27371604
ECLASS-11.0	27371604
ECLASS-11.1	27371604
ECLASS-12.0	27371604
ECLASS-13.0	27371604
ECLASS-14.0	27371604
ETIM-5.0	EC001504
ETIM-6.0	EC001504
ETIM-7.0	EC001504
ETIM-8.0	EC001504
customs tariff number	85414900
EAN	4048879021753
Packaging unit	1

**Electrical data | Input**

Input voltage DC min.	10 V
Input voltage DC max.	53 V
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	5 V
Current input DC	10 mA

**Electrical data | Output**

Voltage drop DC max.	0,1 V
Quiescent current OFF max.	0,025 mA
Switch on delay max.	2 ms
Switch off delay max.	5 ms
Voltage switching DC min.	5 V
Switching voltage DC max.	48 V
Switching current min.	1 mA
Switching current max.	6 A
Switching frequency ohmic max.	1 Hz
Switching frequency inductive max.	0,1 Hz

**Diagnostics**

Status indication LED	yellow
-----------------------	--------

**Device protection | Electrical**

Rated insulation voltage	2.750 V
--------------------------	---------

**Device protection | Media**

Flame resistance	flame retardant
------------------	-----------------

**Mechanical data | Material data**

Material housing	Plastic
Color housing	black

**Mechanical data | Mounting data**

Height	78 mm
--------	-------

Width	6,2 mm
Depth	70 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
Operating temperature max.	60 °C

**Connection type 4**

Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	13 +
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	14
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	+ A 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	- A 2