

Reset button with 1 push button

In a IP65 enclosure

Art.No.: 69010

Weight: 0.103 kg

Country of origin: DE

Model designation: R-Button 42 1NO M12(4)

R-Button / 42 1NO M12(4)

with M12 connection

4-pole

1 button (1 NO contact)

Delivery contents:




Flat lens, transparent clear, red, yellow, green, blue

Label plates, O, I, R

mounting with clip on the back side

Link to Product

Illustration



Product may differ from Image



Header

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-01-28

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Material short text	R-Button 42 1NO M12(4)
Commercial data	
URL Webshop	https://shop.murrelektronik.com/69010
GTIN	4048879594288
ECLASS-6.0	27371228
ECLASS-6.1	27371228
ECLASS-7.0	27371228
ECLASS-7.1	27371228
ECLASS-8.0	27371228
ECLASS-8.1	27371228
ECLASS-9.0	27371228
ECLASS-9.1	27371228
ECLASS-10.0.1	27371228
ECLASS-10.1	27371228
ECLASS-11.0	27371228
ECLASS-11.1	27371228
ECLASS-12.0	27371228
ECLASS-13.0	27371228
ECLASS-14.0	27371228
ETIM-5.0	EC000225
ETIM-6.0	EC000225
ETIM-7.0	EC000225
ETIM-8.0	EC000225
customs tariff number	85365080
EAN	4048879594288
Packaging unit	1
Electrical data Output	
Switching current (AC-15)	15 A
Switching current (DC-13)	2,2 A
Utilization category AC-15 (EN IEC 60947-5-1)	1.5 A @ 240 V
Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V
Device protection	
Condition lifetime	load-dependent, temperature dependent
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	0 cycles
Device protection Mechanical	
Mechanical endurance	0 cycles
Mechanical data	
Bounce time max.	10 ms
Mechanical data Material data	
Material contact	AgNi
Mechanical data Mounting data	
Height	29 mm
Width	124 mm
Depth	42 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Ambient temperature (storage, transport)	-25 °C

Connection type 1

Family construction form	M12
No. of poles	4
Coding	A
Gender	male
Color contact carrier	black
PIN 1	NO
PIN 4	NO