

Emergency-stop pushbutton with 2 positive opening contacts

in a IP65 enclosure

Art.No.: 69041

Weight: 0.177 kg

Country of origin: DE

Model designation: E-Stop 72 2NC M12(5)



E-Stop 72 2NC M12(5)

with M12 connection


5-pole

Emergency-Stop button

2 NC (positively-opening)

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

E-Stop 72 2NC M12(5)

Commercial data

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-01-16

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

URL Webshop	https://shop.murrelektronik.com/69041
GTIN	4048879594684
ECLASS-6.0	27371244
ECLASS-6.1	27371244
ECLASS-7.0	27371244
ECLASS-7.1	27371244
ECLASS-8.0	27371244
ECLASS-8.1	27371244
ECLASS-9.0	27371244
ECLASS-9.1	27371244
ECLASS-10.0.1	27371244
ECLASS-10.1	27371244
ECLASS-11.0	27371244
ECLASS-11.1	27371244
ECLASS-12.0	27371244
ECLASS-13.0	27371244
ECLASS-14.0	27371244
ETIM-5.0	EC002034
ETIM-6.0	EC002034
ETIM-7.0	EC002034
ETIM-8.0	EC002034
customs tariff number	85365080
EAN	4048879594684
Packaging unit	1

Electrical data | Output

Switching current (AC-15)	30 A
Switching current (DC-13)	2,2 A
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 250 V
Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V

Device protection

Condition lifetime	load-dependent, temperature dependent
--------------------	---------------------------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	0 cycles

Device protection | Mechanical

Mechanical endurance	0 cycles
Operating life B10d	250.000 cycles

Mechanical data

Bounce time max.	9 ms
------------------	------

Mechanical data | Material data

Material contact	AgNi
------------------	------

Mechanical data | Mounting data

Height	103 mm
Width	72 mm
Depth	91 mm
Mounting method	screwed

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-25 °C

Technical Data | Reliability

Lambda normally closed contact 20 %

Connection type 1

Family construction form	M12
No. of poles	5
Coding	A
Gender	male
Color contact carrier	black
PIN 1	NC 1
PIN 2	NC 2
PIN 4	NC 1
PIN 5	NC 2