

S-Lamp 22 L M12(4)

Lamp

Art.No.: 69065
Weight: 0.012 kg
Country of origin: HU
Model designation: S-Lamp 22 L M12(4)


S-Lamp 22 L M12(4)
Lamp
Mounting hole 22,3 mm
Connection M12 (4-pin)

Link to Product

Illustration



Product may differ from Image



Header

Material short text S-Lamp 22 L M12(4)

Commercial data

URL Webshop	https://shop.murrelektronik.com/69065
GTIN	4065909019245
ECLASS-6.1	27371223
ECLASS-7.0	27371223
ECLASS-7.1	27371223
ECLASS-8.0	27371223
ECLASS-8.1	27371223
ECLASS-9.0	27371223
ECLASS-9.1	27371223
ECLASS-10.0.1	27371223
ECLASS-10.1	27371223
ECLASS-11.0	27371223
ECLASS-11.1	27371223
ECLASS-12.0	27371223
ECLASS-13.0	27371223

ECLASS-14.0	27371223
ETIM-5.0	EC000272
ETIM-6.0	EC000272
ETIM-7.0	EC000272
ETIM-8.0	EC000272
customs tariff number	85318070
EAN	4065909019245
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	20 V
Operating voltage DC max.	28 V
Operating current max.	12 mA
Rated operating current	0,01 A

Electrical data | Input

Short-circuit current	1.000 A
-----------------------	---------

Installation | Connection

Family construction form	M12
--------------------------	-----

Installation | Pin assignment

Coding	A
No. of poles	4

Device protection | Electrical

Installation height max. ASL	2.000 m
Degree of protection front (EN IEC 60529)	IP66, IP67, IP69
Degree of protection back (EN IEC 60529)	IP66, IP67
Pollution Degree	2
Short circuit protective device (SCPD)	fuse 250 V / 0.1 A / 1.5 kA gG quick
Overvoltage category (EN 60950-1)	II
Rated insulation voltage	250 V

Device protection | Mechanical

UL enclosure type rating front side	type 4X
-------------------------------------	---------

Device protection | Media

Salt-spray resistance (IEC 60068-2-11)	Yes
--	-----

Mechanical data

Shape collar	round
Color collar	black
Color	black
Can be illuminated	Yes
Type of illuminant	LED
Color illuminant	white

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	29,8 mm
Width	40 mm
Mounting method	Threaded ring
Installation height	9,8 mm
Mounting depth	36,4 mm
Mounting hole	22,3 mm
Grid min.	30 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Derating from	40 °C
Ambient temperature (storage, transport)	-40 °C ... 90 °C
Relative humidity (operation)	93 %

Connection type 2

Family construction form	M12
No. of poles	4
Coding	A
Gender	male
Color contact carrier	black
PIN 2	LED (A)
PIN 3	LED (K)
Family construction form	M12
No. of poles	4
Coding	A
Gender	male
PIN 2	LED (A)
PIN 3	LED (K)