

Xelity 8TX managed switch 8 port 1000Mbit ProfiNet IP20

Art.No.: 58825

Weight: 0.164 kg

Country of origin: DE

Model designation: Xelity 8TX M GE PN

Murrelektronik's Xelity product family brings managed switching to the control cabinet: compact, IP20-rated, and easily mounted on a DIN rail.


Available with 4, 6, 8, or 16 Gigabit RJ45 ports, and offered as a PROFINET switch, EtherNet/IP switch, or a pure managed switch.


Network expansion is achieved via plug-and-play with low power consumption. A microSD card enables device replacement without the need for reconfiguration.

Management functions are available via web server, SNMP, and REST API, including MRP, RSTP, VLAN 802.1Q, QoS, and a 1:1 NAT function.

For diagnostics, a cable tester with fault localization, a topology viewer, and detailed port statistics are integrated.

Security features such as Port Security, IEEE 802.1X, and RADIUS, along with an OpenVPN client for remote maintenance, round out the functional scope.

[Link to Product](#)**Illustration**



Product may differ from Image



Commercial data

URL Webshop	https://shop.murrelektronik.com/58825
GTIN	4065909004722
EU-Customs tariff number	85176200
US-Customs tariff number	8517620090
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-7.1	19170106
ECLASS-8.0	19170106
ECLASS-8.1	19170106
ECLASS-9.0	19170106
ECLASS-9.1	19170106
ECLASS-10.0.1	19170401
ECLASS-10.1	19170401
ECLASS-11.0	19170401
ECLASS-11.1	19170401
ECLASS-12.0	19170401
ECLASS-13.0	19170401
ECLASS-14.0	19170401
ETIM-7.0	EC000734
ETIM-8.0	EC000734
customs tariff number	85176200
EAN	4065909004722
Packaging unit	1

Electrical data | Supply

Protective measure	SELV/PELV
Operating voltage type	DC
Operating voltage DC	12 V / 24 V
Operating voltage DC min.	9 V
Operating voltage DC max.	30 V
Power failure bridging time	10 ms
Idle current max.	150 mA
Current consumption max.	450 mA
Power consumption max.	4,1 W

Industrial Communication	
Number of HW interfaces (Industrial Ethernet)	8
Industrial communication Bus data	
Supported protocol	PROFINET
Industrial communication Ethernet/IP	
Addressing	DHCP
CIP Sync	Yes
Device Level Ring (DLR)	No
Shared device/input	No
Industrial communication Ethernet functionality	
Switch type	managed
Switching procedure	Store & forward
duplex	Full or half duplex
Auto-negotiation	Yes
Auto-crossover	Yes
Auto-polarity	Yes
Energy-efficient Ethernet (IEEE 802.3az)	Yes
Topology	line, star, ring, net
Line topology cascading max.	64
Ring topology	MRP, RSTP
Net topology	RSTP
Industrial communication PROFINET	
Conformance Class	B
addressing	DCP
PROFIenergy	No
Netload Class	III
Specification	V2.4
Cycle time min.	128 ms
IRT-network communication	No
MRP client	Yes
Fast-Start-Up (FSU)	No
Shared device/input	No
Industrial communication IIoT functions	
Webserver	HTTPS, HTTP
Remote maintenance	Open VPN client
Industrial communication Security	
Webserver	HTTPS certificate management, Password change at first login (FPC), Local user administration, TLS V1.2 and higher
Access control	Network Access Control (NAC 802.1X), RADIUS-Server
Industrial communication Memory interface	
Memory card (type)	Micro SD
Memory card max. (capacity)	32 GB
Switch Management	
IP preset	0.0.0.0/24
Priorization type (IEEE 802.1D, IEEE 802.1p)	CoS, DSCP, (Mapping CoS/DSCP)
NAT	1:1
QoS (IEEE 802.1p)	8 queues
VLAN managed (IEEE 802.1Q)	Yes
VLANs max. (IEEE 802.1Q)	64
MRP (IEC 62439-2)	Client, Manager
RSTP (IEEE 802.1D-2004, IEC 62439-1)	Default off

Simple Network Management Protocol (SNMP) v1 + v2c + v3 (default active)

AutoUpdateX compatible	≥V3.6
Time synchronization	NTP client, Real-time clock, NTP-Server, PTP
Addressing	SSH-Befehlszeile, DCP, BOOTP/DHCP client, Web based management, MIB-Support
Configuration file management	Webserver, FTP, TFTP, SFTP, HTTP, Micro SD

Diagnostics

Alarm contact	Yes
LED display	Ethernet connection/data traffic, Fieldbus status, power supply, Device state
System information	Input voltage, Device information, device temperature, Overload indicator
RMON	Yes
Network information	Neighborhood detection (LLDP, IEEE 802.1AB), MAC notifications
Port mirroring	N:1, 1:1
Syslog	Yes
SNMP traps	Yes

Device protection | Electrical

Installation height max. ASL	3.000 m
Degree of protection (EN IEC 60529)	IP20
Protection class (EN IEC 61140)	III
Additional condition overload protection	Circuit Breakers 9 A
Invers-polarity protection	Yes
Pollution Degree	2
Over voltage protection	No
Overload protection device supply	Yes
Protective circuitry input	Internal, Suppressor diode
Overvoltage category (EN 60664-1)	I

Device protection | Mechanical

Free fall (EN 61131-2)	0,3 m
Shock resistance (EN IEC 60068-2-27)	15 g 11 ms 6 x (X-, Y-, Z-axis)
Vibration resistance (EN IEC 60068-2-6)	3,5 mm (5 ... 9 Hz), 1 g (9 ... 150 Hz), XYZ-Axis

Mechanical data | Material data

housing	ABS, PC
Combustibility class housing (UL94)	V-0
Color housing	gray

Mechanical data | Mounting data

Net weight	164 g
Height	109 mm
Width	41,6 mm
Depth	86,4 mm
Mounting method	Snap-in connector
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Electromagnetic compatibility

Interference emission	EN IEC 61000-6-4
Immunity to interference	EN IEC 61000-6-1, EN IEC 61000-6-2

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	75 °C
Ambient temperature (operation)	-40 °C ... 70 °C
Derating	min. 60 °C
Ambient temperature (storage, transport)	-40 °C ... 85 °C
Relative humidity (operation)	5 % ... 95 %
Additional condition relative humidity	no condensation

Relative humidity (storage, transport)	max. 95 %
--	-----------

Assembly location	Interior
-------------------	----------

Technical Data | Reliability

MTTF (EN/IEC 61709, EN ISO 13849-1, SN 29500)	101 a @ 40 °C
---	---------------

Environmental product conformity

REACH ((EC) 1907/2006)	compliant
REACH SVHC ((EC) 1907/2006)	Lead (Pb) CAS 7439-92-1
RoHS (2011/65/EU, (EU) 2015/863)	compliant
RoHS-Exemption (2011/65/EU)	7(a), 7(c)-I
China RoHS (SJ/T 11364, GB/T 26572)	EFUP-20
California Proposition 65	Nickel (Ni) CAS 7440-02-0
WEEE (2012/19/EU)	Category 6
Halogen-free-Material	not halogen-free
Pb-free-Material	No
Date of evaluation	2022-04

Conformity

Product standard	EN/IEC 61010-1, EN IEC 61010-2-201
CE	2014/30/EU, 2011/65/EU
UKCA	The Electromagnetic Compatibility Regulations 2016, The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012

Approvals

UL Listed (US, CA)	E201820
KC	Yes

Connection type 2

Connection type 1	8
Family construction form	RJ45
No. of poles	8
Gender	female
Color contact carrier	black
PIN 1	DA +
PIN 2	DA -
PIN 3	DB +
PIN 4	DC +
PIN 5	DC -
PIN 6	DB -
PIN 7	DD +
PIN 8	DD -
Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	24 V DC (UB 1)
PIN 2	0 V
PIN 3	PE
PIN 4	n.c.