

**M12 female 90° A-cod. screw terminal**

 4-pol., max. 0,75mm<sup>2</sup>, 4 - 6mm

Art.No.: 7000-12981-0000000

Weight: 0.025 kg

Country of origin: DE

Model designation: MSDL0-T-SK 4..6MM

Female 90°




M12, 4-pole

Screw terminals

Sealing range (cable Ø): 4...6 mm

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)
**Illustration**


Product may differ from image


**Header**

Material short text

MSDL0-T-SK 4..6MM

**Side 1**

Family construction form	M12
No. of poles	4
Coding	A
Gender	female
Mounting method	inserted, screwed
Threaded hole	M12 x 1
Tightening torque	0,6 Nm
Width across flats	SW18
Cable outlet	angled
Material	PA
Material contact	Brass
Degree of protection (EN IEC 60529)	IP67

**Side 2**

Mounting method	Field-wireable
Cable outlet	straight

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/7000-12981-0000000">https://shop.murrelektronik.com/7000-12981-0000000</a>
GTIN	4048879201520
ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-7.1	27440102
ECLASS-8.0	27440102
ECLASS-8.1	27440102
ECLASS-9.0	27440116
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440102
ECLASS-11.0	27440106
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002635
ETIM-6.0	EC002635
ETIM-7.0	EC002635
ETIM-8.0	EC002635
customs tariff number	85366990
EAN	4048879201520
Packaging unit	1

**Electrical data | Supply**

Operating voltage AC max.	250 V
Operating voltage DC max.	250 V
Current operating per contact max.	4 A

**Diagnostics**

Status indication LED	No
-----------------------	----

**Installation**

Rotation option	90° (4 outlet directions)
Connection cross section max.	0,75 mm <sup>2</sup>
Cross section connection without wire end ferrule AWG max.	18 AWG

**Installation | Connection**

Tightening torque	0,6 Nm
-------------------	--------

**Device protection**

Shielded	No
----------	----

**Device protection | Electrical**

Additional condition protection degree	inserted, screwed
--	-------------------

Pollution Degree	3
------------------	---

Overvoltage category (EN 60664-1)	II
-----------------------------------	----

Overvoltage category (EN 60950-1)	II
-----------------------------------	----

Rated surge voltage	2,5 kV
---------------------	--------

Material group (IEC 60664-1)	III
------------------------------	-----

**Mechanical data | Material data**

Material housing	PA
------------------	----

Locking material	Zinc die-casting
------------------	------------------

Coating locking	nickel plated
-----------------	---------------

**Mechanical data | Mounting data**

Height	35 mm
--------	-------

Width	35 mm
-------	-------

Depth	20 mm
-------	-------

Mounting method	inserted, screwed, Shaking protection
-----------------	---------------------------------------

Clamping range min.	4 mm
---------------------	------

Clamping range max.	6 mm
---------------------	------

**Environmental characteristics | Climatic**

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max.	85 °C
----------------------------	-------

**Important installation notes**

Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
------------------------	---

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
-----------------------	---

Note on mounting	The plug connectors must not be connected or disconnected under load. Non-compliance and improper use can result in personal injury., The user must take suitable safety precautions to ensure that the plug connector cannot be accidentally disconnected., To
------------------	---

**Conformity**

Product standard	EN IEC 61076-2-101 (M12)
------------------	--------------------------