

SVS VALVE PLUG FORM B 10 MM FIELD-WIREABLE

230V LED+VDR M16x1.5

Art.No.: 7000-29721-0000000

Weight: 0.030 kg

Country of origin: CN

Model designation: MSVS-LB4W-M16

Form B (10 mm)


 230 V AC $\pm 10\%$

LED and RC



metric


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)
Illustration


Height: 41 mm





Product may differ from Image



Side 1

Mounting method	inserted, screwed
Degree of protection (EN IEC 60529)	IP65

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-29721-0000000
customs tariff number	85366990
EAN	4048879187244
Packaging unit	1

Electrical data

Drop-out delay time max.	15 ms
Holding power max.	50 W

Electrical data | Supply

Operating voltage AC	230 V
Operating voltage AC min.	207 V
Operating voltage AC max.	253 V
Current operating per contact max.	1 A
Cut-off peak voltage max.	450 V
Current consumption max.	12 mA

Diagnostics

Status indication LED	yellow
-----------------------	--------

Installation

Connection cross section max.	1.5 mm ²
-------------------------------	---------------------

Installation | Connection

Tightening torque	0.4 Nm
Mounting set	M16 x 1.5

Device protection | Electrical

Additional condition protection degree	locked, with screw connection, inserted
--	---

Mechanical data | Mounting data

Fastening screw	M3x31
Clamping range min.	5 mm
Clamping range max.	10 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.