

Adapter M12 female 0° X-cod. / RJ45 0°

8-pol., shielded, CAT6A

Art.No.: 7000-51531-0000000

Weight: 0.048 kg

Country of origin: RO

Model designation: Adapter M12 X-Cod. auf RJ45 gerade

Adapter

M12 – RJ45

Female straight – female straight

8-pole




X-coded

Gigabit

Ethernet CAT6A

Shielded

Cap nut

[Link to Product](#)**Illustration**

Product may differ from Image



Header	
Material short text	Adapter M12 X-Cod. auf RJ45 gerade
Side 1	
Family construction form	M12
No. of poles	8
Coding	X
Mounting method	inserted, screwed
Threaded hole	M16 x 1.5
Tightening torque	0,6 Nm
Width across flats	SW18
Material contact	Copper alloy
Degree of protection (EN IEC 60529)	IP65, IP67
Side 2	
Family construction form	RJ45
No. of poles	8
Mounting method	pluggable
Degree of protection (EN IEC 60529)	IP20
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-51531-0000000
GTIN	4048879699402
ECLASS-6.0	27143423
ECLASS-6.1	27279221
ECLASS-7.0	27440104
ECLASS-7.1	27440104
ECLASS-8.0	27440104
ECLASS-8.1	27440104
ECLASS-9.0	27440106
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440106
ECLASS-11.0	27440106
ECLASS-11.1	27440106
ECLASS-12.0	27440106
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002640
ETIM-6.0	EC002640
ETIM-7.0	EC002640
ETIM-8.0	EC002640
customs tariff number	85366990
EAN	4048879699402
Packaging unit	1
Electrical data Supply	
Operating voltage AC max.	48 V
Operating voltage DC max.	60 V
Industrial Communication	
Supported protocol	Ethernet
Data transmission rate max.	10 Gbit/s
Transfer parameters	CAT6A
Installation Connection	
Width across flats	SW18

Mating cycles min.	100
--------------------	-----

Device protection

Shielded	Yes
----------	-----

Mechanical data | Material data

Material housing	Zinc die-casting
------------------	------------------

Material contact	Copper alloy
------------------	--------------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max.	85 °C
----------------------------	-------

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
------------------------	---

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
-----------------------	---

Conformity

Product standard	EN/IEC 61076-2-109 (X-coded), EN 45545-2
------------------	--