

Push Pull Power / Push Pull Power AIDA




PUR 5x2.5 gy UL/CSA+drag ch. 1.5m

Art.No.: 7000-99641-9620150
Weight: 0.479 kg
Country of origin: CZ
Model designation: MSWPAL0-WPA-U962_1.5



Male straight – male straight
PPP – PPP, 5-pole
Push Pull Power
Further cable lengths on request.
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



1	BN 3	1
2	BU 2	2
3	BK 1	3
4	WH 4	4
5	GN YE	5



Product may differ from Image

Cable length	1,50 m
Side 1	
Family construction form	Push Pull Power
No. of poles	5
Gender	female
Cable outlet	straight
Degree of protection (EN IEC 60529)	IP67, IP65
Side 2	
Family construction form	Push Pull Power
No. of poles	5
Gender	female
Cable outlet	straight
Degree of protection (EN IEC 60529)	IP67, IP65
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-99641-9620150
GTIN	4048879113694
EU-Customs tariff number	85444290
US-Customs tariff number	8544429090
ECLASS-6.0	27279218
ECLASS-6.1	27279218
ECLASS-7.0	27279218
ECLASS-7.1	27279218
ECLASS-8.0	27279218
ECLASS-8.1	27279218
ECLASS-9.0	27060327
ECLASS-9.1	27060311
ECLASS-10.0.1	27060311
ECLASS-10.1	27060311
ECLASS-11.0	27060311
ECLASS-11.1	27060311
ECLASS-12.0	27060327
ECLASS-13.0	27060311
ECLASS-14.0	27060311
ETIM-5.0	EC002599
ETIM-6.0	EC002599
ETIM-7.0	EC002599
ETIM-8.0	EC002599

ETIM-9.0	EC002599
ETIM-10.0	EC002599
customs tariff number	85444290
EAN	4048879113694
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	24 V
Operating voltage DC max.	24 V
Current operating per contact max.	16 A

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67, IP65
Additional condition protection degree	inserted, screwed
Rated surge voltage signal contacts	4 kV

Mechanical data | Material data

housing	Zinc die-casting
Coating housing	nickel plated

Mechanical data | Mounting data

Looking techniques	Push Pull
--------------------	-----------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Installation | Cable

Cable identification	962
Cable Type	3
Function cable	Power
Cable weight	173 g/m
UL AWM Style	21223 / 11560
Stranding	1 × 5 wires around core filler twisted
Filler	Yes
Wire arrangement	GNYE, BU 2, BK 1, WH 4, BN 3
Material wire insulation	PP
Amount wires	5
Outer diameter insulation	2.85 mm ± 0.1 mm
Conductor crosssection (wire)	2,5 mm ²
Material conductor wire	Stranded copper wire, bare
Core construction (wire)	140 × 0.15 mm
Ingredient freeness wire insulation	lead-free, cadmium-free, CFC-free, halogen-free, silicone-free
Material jacket	PUR
Outer-diameter (jacket)	9.5 mm ± 5 %
Jacket Color	gray / RAL 7040
Freedom from ingredients (jacket)	lead-free, cadmium-free, CFC-free, halogen-free, silicone-free
Material property (jacket)	abrasion-resistant, low adhesion, good machinability, matte
Conductor resistance (wire)	7.98 Ω/km @ 20 °C
Nominal voltage max.	1.000 V
Withstand voltage (wire - wire)	10 kV @ 60 s
Withstand voltage (wire - jacket)	10 kV @ 60 s
Current load capacity max. (wire)	19,5 A

Current load capacity (standard)	to DIN VDE 0298-4
Operating temperature (static)	-50 °C ... 80 °C / 90 °C @ 10000 h Operation
Operating temperature (dynamic)	-25 °C ... 80 °C / 90 °C @ 10000 h Operation
Flame resistance	IEC 60332-1-2, IEC 60332-2-2, UL 1581 § 1080, CSA FT2
Oil resistance	IEC 60811-404
Chemical resistance	good
Other resistances	good resistance to gasoline, resistant to hydrolysis, resistant to microbes
Notes	application-related testing
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter
No. of bending cycles (C-track)	5 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C
Travel speed (C-track)	3.3 m/s @ 25 °C
Acceleration (C-track)	5 m/s² @ 25 °C
No. of torsion cycles	5 Mio.
Torsion stress	± 180 °/m
Torsion speed	35 cycles/min