

Cable drum Ø 355mm

PUR 12x0.25 gy UL/CSA+drag ch. 100m

Art.No.: 7000-C0101-3010000

Weight: 7.504 kg

Country of origin: DE

Model designation: 100m Kabel 10081383(301)auf Spule 01

The selection of cables suitable for cable reels must always be based on the specific application. In particular, the mechanical and dynamic loads encountered during operation must be taken into account. These include, among other things, permissible bending radii, drag chain and continuous motion properties, torsional characteristics, and other environmental and application-specific requirements.



Cable drum (100 m)

PUR (UL/CSA)

12× 0.25 mm², grey

suitable for C-tracks

2 Mio.

Link to Product**Illustration**

Product may differ from Image

Commercial data

URL Webshop

<https://shop.murrelektronik.com/7000-C0101-3010000>

GTIN

4048879451765

EU-Customs tariff number	85444995
US-Customs tariff number	8544499000
ECLASS-6.0	27062011
ECLASS-6.1	27061801
ECLASS-7.0	27061801
ECLASS-7.1	27061801
ECLASS-8.0	27061801
ECLASS-8.1	27061801
ECLASS-9.0	27061801
ECLASS-9.1	27061801
ECLASS-10.0.1	27061801
ECLASS-10.1	27061801
ECLASS-11.0	27061801
ECLASS-11.1	27061801
ECLASS-12.0	27061801
ECLASS-13.0	27061801
ECLASS-14.0	27061801
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444995
EAN	4048879451765
Packaging unit	1

Mechanical data | Mounting data

Cable length	100 m
--------------	-------

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Installation | Cable

Stranding	1 × 3 wires stranded
Stranding (type 2)	1 × 9 wires stranded around stranding combination
Banding	Fleece
Wire arrangement	(GYPK, VT, RDBU), BN, RD, GY, BK, YE, PK, GN, WH, BU
Material wire insulation	PP
Amount wires	12
Outer diameter insulation	1.25 mm ± 0.05 mm
Conductor crosssection (wire)	0,25 mm²
Material conductor wire	Stranded copper wire, bare
Core construction (wire)	32 × 0.1 mm
Ingredient freeness wire insulation	lead-free, cadmium-free, CFC-free, halogen-free, silicone-free
Material jacket	PUR
Outer-diameter (jacket)	7 mm ± 5 %
Jacket Color	gray / RAL 7040
Freedom from ingredients (jacket)	lead-free, cadmium-free, CFC-free, halogen-free
Material property (jacket)	abrasion-resistant, low adhesion, good machinability, matte
Conductor resistance (wire)	76 Ω/km @ 20 °C
Nominal voltage max.	300 V
Withstand voltage (wire - wire)	1.5 kV @ 60 s
Withstand voltage (wire - jacket)	1.5 kV @ 60 s
Current load capacity max. (wire)	3 A
Current load capacity (standard)	to DIN VDE 0298-4

Electric capacitance	80.000 pF/km
Isolation resistance	10 MΩ × km
Operating temperature (static)	-40 °C ... 80 °C
Operating temperature (dynamic)	-20 °C ... 80 °C
Operating temperature (drag chain)	-20 °C ... 80 °C
Flame resistance	UL 1581
Oil resistance	IEC 60811-404
Chemical resistance	good
Other resistances	good resistance to gasoline, resistant to hydrolysis, resistant to microbes
Notes	application-related testing
Bending radius (fixed)	10 × Outer diameter
Bending radius (dynamic)	15 × Outer diameter
No. of bending cycles (C-track)	3 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C horizontal
Travel speed (C-track)	2 m/s @ 25 °C
Acceleration (C-track)	10 m/s² @ 25 °C