

Cable drum Ø 500mm

PUR 16x0.34+3x0.75 gy drag ch. 100 m

Art.No.: 7000-C0501-3980000

Weight: 19.509 kg

Country of origin: PL

Model designation: 100m Kabel 10081338(398)auf Kabeltrommel

The selection of cables suitable for cable reels must always be based on the specific application. In particular, the mechanical and dynamic loads encountered during operation must be taken into account. These include, among other things, permissible bending radii, drag chain and continuous motion properties, torsional characteristics, and other environmental and application-specific requirements.

PUR/PVC



16× 0.34 + 3× 0.75 mm²

gray

suitable for C-tracks

2 Mio.

Cable drum (100 m)

Link to Product**Illustration**

Product may differ from Image

Commercial data

URL Webshop

<https://shop.murrelektronik.com/7000-C0501-3980000>

GTIN	4065909050125
EU-Customs tariff number	85444995
ECLASS-6.0	27062011
ECLASS-7.0	27062011
ECLASS-7.1	27062011
ECLASS-8.0	27062011
ECLASS-8.1	27062011
ECLASS-9.0	27062011
ECLASS-9.1	27062011
ECLASS-10.0.1	27060106
ECLASS-11.0	27060106
ECLASS-13.0	27060106
ECLASS-14.0	27060106
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444995
EAN	4065909050125
Packaging unit	1

Mechanical data | Mounting data

Cable length	100 m
--------------	-------

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Installation | Cable

Stranding	1 × 7 wires around core filler twisted
Stranding (type 2)	1 × 12 wires stranded around stranding combination
Filler	Yes
Wire arrangement	(WH, GYPK, BNGN, YE, GNWH, GN, RDBU), BNGY, BK, GYWH, RD, BNYE, PK, YEWH, GY, BU, BN, GNYE, VT
Material wire insulation	PVC
Amount wires	16
Outer diameter insulation	1.3 mm ± 0.1 mm
Conductor crosssection (wire)	0,34 mm²
Material conductor wire	Stranded copper wire, bare
Core construction (wire)	19 × 0.15 mm
Material properties wire insulation	good machinability
Ingredient freeness wire insulation	lead-free, cadmium-free, CFC-free, silicone-free
Electrical function wire (type 2)	Power
Material wire insulation (type 2)	PVC
Amount wires (type 2)	3
Outer diameter wire insulation (type 2)	1.8 mm ± 0.1 mm
Conductor crosssection (wire type 2)	0,75 mm²
Material conductor wire (type 2)	Stranded copper wire, bare
Core construction (wire type 2)	42 × 0.15 mm
Material properties wire insulation (type 2)	good machinability
Ingredient freeness wire insulation (type 2)	lead-free, cadmium-free, CFC-free, silicone-free
Material jacket	PUR
Outer-diameter (jacket)	10 mm ± 5 %
Jacket Color	gray / RAL 7040
Material inner jacket	PVC
Color (inner jacket)	gray

Freedom from ingredients (jacket)	lead-free, cadmium-free, CFC-free, silicone-free
Material property (jacket)	abrasion-resistant, low adhesion, good machinability, matte
Conductor resistance (wire)	57 Ω /km @ 20 °C
Conductor resistance (wire type 2)	26 Ω /km @ 20 °C
Max. rated voltage (conductor - ground)	300 V
Max. rated voltage (conductor - conductor)	300 V
Withstand voltage (wire - wire)	2 kV @ 60 s
Withstand voltage (wire - jacket)	2 kV @ 60 s
Current load capacity max. (wire)	4 A
Current load capacity max. Wire (type 2)	12 A
Current load capacity (standard)	to DIN VDE 0298-4
Operating temperature (static)	-30 °C ... 80 °C
Operating temperature (dynamic)	-5 °C ... 70 °C
Operating temperature (drag chain)	-5 °C ... 60 °C
Flame resistance	UL 1581 § 1090, CSA FT2, IEC 60332-2-2
Oil resistance	IEC 60811-404
Chemical resistance	good
Other resistances	good resistance to gasoline, resistant to hydrolysis, resistant to microbes
Notes	application-related testing
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter
No. of bending cycles (C-track)	2 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C
Travel speed (C-track)	2 m/s @ 25 °C
Acceleration (C-track)	10 m/s ² @ 25 °C